




MJC15-3-A

Ruland MJC15-3-A, 3mm Jaw Coupling Hub, Aluminum, Clamp Style, 15.0mm OD, 7.6mm Length




Description

Ruland MJC15-3-A is a clamp zero-backlash jaw coupling hub with a 3mm bore, 15.0mm OD, and 7.6mm length. It is a component in a three-piece design consisting of two aluminum hubs and an elastomeric insert called the spider creating a lightweight low inertia coupling capable of speeds up to 8,000 RPM. This three-piece design allows for a highly customizable coupling that easily combines clamp or set screw hubs with inch, metric, keyed, and keyless bores. Spiders are available in three durometers allowing the user to tailor coupling performance to their application. Ruland jaw couplings have a balanced design for reduced vibration at high speeds. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MJC15-3-A is machined from bar stock that is sourced exclusively from North American mills and is RoHS3 and REACH compliant. It is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	3 mm	Shaft Penetration B1	7.6 mm
Outer Diameter (OD)	15.0 mm	Bore Tolerance	+0.03 mm / -0.00 mm
Hub Width (LH)	7.6 mm	Length (L)	21.8 mm
Forged Clamp Screw	M2	Number of Screws	1 ea
Screw Material	Alloy Steel	Screw Finish	Black Oxide
Hex Wrench Size	1.5 mm	Seating Torque	0.6 Nm
Maximum Speed	8,000 RPM	Weight (lbs.)	0.0084
Temperature	-10°F to 180°F (-23°C to 82°C)	Material Specification	2024-T351 Aluminum Bar
Finish	Bright	Finish Specification	Bright
Manufacturer	Ruland Manufacturing	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
UPC	63452906764	Country of Origin	USA
Tariff Code	8483.60.8000		

Note 1	Stainless steel hubs are available upon request.
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the spiders. Under normal/typical conditions the hubs are capable of holding up to the nominal torque of the spiders. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the nominal torque of the spiders. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.
Prop 65	 WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .

Installation Instructions

1. Align the bores of the MJC15-3-A jaw coupling hubs on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (See spider for misalignment parameters.)
2. Fully tighten the M2 screw(s) on the first hub to the recommended seating torque of 0.6 Nm using a 1.5 mm hex torque wrench.
3. Insert a spider into the jaws of one hub until the raised points contact the base of the hub.
4. Insert the jaws of the second hub into the spider openings until the raised points contact the base of the second hub. Some force will be required to insert the second hub. This is normal.
5. Assure that a gap is maintained between the two hubs so there is no metal to metal contact. Fully tighten the screw(s) on the second hub to the recommended seating torque.