


FEATURES

- **Metal Detectable:**
Enhances safety by allowing detection in food and pharmaceutical environments
- **Nylon Material:** Provides strength and flexibility for reliable cable management
- **Length 100 mm:** Suitable for a variety of bundling applications
- **Maximum Bundle Diameter 22 mm:**
Accommodates a wide range of cable sizes
- **Tensile Strength 6 kg:**
Ensures secure fastening of cables
- **Temperature Range -40 °C to 85 °C:** Suitable for diverse environmental conditions
- **UL 94HB Fire Behaviour:**
Offers basic flame retardancy for added safety
- **RoHS Compliant:** Meets environmental and safety standards

RS PRO Metal Detectable Cable Tie, 100 mm Nylon

RS Stock No: 656-072



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO metal detectable cable ties are designed for secure bundling and organising of cables, particularly in environments where metal detection is crucial. Made from durable nylon, they are ideal for use in food processing and pharmaceutical industries where contamination prevention is essential.

General Specifications

| | |
|------------------|------------------|
| Colour | Blue |
| Product Type | Cable Tie |
| Sub Type | Metal Detectable |
| Tensile Strength | 6 kg |

Protection Category

| | |
|----------------|---------|
| Fire Behaviour | UL 94HB |
| UV Resistant | No |

Mechanical Specifications

| | |
|-------------------------|--------|
| Length | 100 mm |
| Material | Nylon |
| Maximum Bundle Diameter | 22 mm |
| Width | 2.5 mm |

Operation Environment Specifications

| | |
|-------------------------------|--------|
| Maximum Operating Temperature | 85 °C |
| Minimum Operating Temperature | -40 °C |

Approvals

| | |
|---------------------|--------------|
| Standards/Approvals | RoHS, UL94HB |
|---------------------|--------------|

