

FEATURES

- Synthetic rubber outer cover
- High tensile steel wire reinforcement
- Suitable for mineral oils, lubricating oils, water glycol, water-oil emulsion hydraulic fluids

RS PRO Hydraulic Hose Assemblies

RS Stock No.: 1102242



Product Description

Part No.	Thread Size	Length
1102242	1/4"	2.0m



Product Description

RS Pro hydraulic hose assembly of 2000 mm has maximum operating pressure of 210 bar. This
flexible hydraulic hose assembly has synthetic rubber outer covering and high tensile steel wire
reinforcing for durability. The hose assembly features straight G 1/4 female connector on first each
end. It has operating temperature range of -40 to +100°C and is suitable for mineral oils, lubricating
oils, water glycol and water-oil emulsion hydraulic fluids applications.

General Specifications

Model	(Note: Not MPN)	
Overall Length	2.0m	
Outside Diameter	13.4mm	
Inside Diameter	1/4"	
Maximum Operating Pressure	210 bar	
Connector A	Straight G 1/4 Female;	
Connector A – Angle	Straight	
Connector A – Gender	Female	
Connector A - Thread Size	1/4"	
Connector A - Thread Standard	G	
Connector B	Straight G 1/4 Female	
Connector B – Angle	Straight	
Connector B - Gender	Female	
Connector B - Thread Size	1/4"	
Connector B - Thread Standard	G	
Dash Size	04	
Inner Hose Material	Buna N (Nitrile); Synthetic Rubber	
Reinforcing Material	1 wire braid	
Cover Material	Synthetic Rubber; Wire Braid;	
Media	Hydraulic Fluids, Lubricants	
Fitting Material	Zinc Plated Steel	
Fitting Type	Crimp	
Braided	1 Wire	
Safety Locking Collar	No	
Burst Pressure	900 bar	
Minimum Operating Temperature	-40°C	
Maximum Operating Temperature	100°C	
Weight	0.18kg	



Suitability

Mineral Oils, Lubricating Oils, Water Glycol, Water-Oil Emulsion Hydraulic Fluids

Classification

eCl@ss Version
UNSPSC Version

Approvals

Compliance/Certifications	EN853 SAE100R1AT

Similar Products

Part No.	Thread Size	Length
1102241	1/4"	0.5m