

**FAG****6210-MA-C3**

Deep groove ball bearing

Deep groove ball bearing 62...-MA, single row,
solid brass cageSchaeffler ID:
0382827200030

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	MA	Solid brass cage, outer ring guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	20 mm	Width
C _r	39.000 N	Basic dynamic load rating, radial
C _{0r}	24.200 N	Basic static load rating, radial
C _{ur}	1.460 N	Fatigue load limit, radial
n _G	13.700 1/min	Limiting speed
n _{gr}	8.200 1/min	Reference speed
≈m	0,56 kg	Weight



Mounting dimensions

$d_{a\min}$	57 mm	Minimum diameter shaft shoulder
$D_{a\max}$	83 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	78,3 mm	Shoulder diameter outer ring
d_1	62 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	14,3	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed