

Product datasheet

Specifications



"PanelSet S3X - stainless steel
304L- Scotch Brite® finish -
H800xW1000xD300 mm."

NSYS3X801030

EAN Code: 3606480731754

Main

Range	Spacial
Product name	Spacial S3X
enclosure type	Multi-purpose
category	Compact enclosure
nominal height	800 mm
nominal width	1000 mm
nominal depth	300 mm
product installation	Wall-mounting
Device composition	1 body 1 lock: door 2 perforated vertical profile drilled: door 2 doors

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	Reversible (120 °)
Lock type	3 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	38 kg

Environment

Standards	IEC 62208 UL CUL
Product certifications	UL 508 type A CAN/CSA 22

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33.000 cm
Package 1 Width	82.000 cm
Package 1 Length	102.000 cm
Package 1 Weight	38.250 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	8
Package 2 Height	218.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	318.000 kg

Logistical informations

Country of origin	BG
--------------------------	----

Contractual warranty

Warranty (in months)	18
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	569 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	390 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	76 kg CO2 eq.
Carbon footprint of the installation phase [A5]	2 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	100 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

Product benefits / Features

High resistance to corrosion

Earthing studs included

Large choice of dimensions & accessories

Built to last

Easy to equip
Easy to maintain

Easy & quick assembly