

## System Accessories

Impact Drills



### For Drills, Impact Drills and Cordless Drills

Pic.	Description	Part no.
<b>For comfortable handling</b>		
41	Depth stop for auxiliary handle 63	1 613 001 005
not illus.	Depth stop for auxiliary handle	2 603 001 019
not illus.	Auxiliary handle with PowerLight	2 602 025 150
42	Universal auxiliary handle for PSB 500 RE/500 RA for PSB 650 RE/750 RCE/750 RCA	2 609 255 727
43	Universal auxiliary handle for PSB 850-2 RE/850-2 RA for PSB 1000-2 RCE/1000-2 RCA	2 609 255 728
not illus.	Auxiliary handle for PSB 1000 RCA, 650 RA, 530 RA for PSB 1000 RPE, 700 RE, PSB 650 RE, 600 RE, 500 RE for PSB 14.4 V-i	2 602 025 102
44	Plastic carrying case for PBH 300 E for impact drills with 400–550 watts for impact drills with 570–600 watts for impact drills with 650–1000 watts for cordless centre-grip screwdrivers for PSB 1000 RCA, 650 RA for PSB 800-2 RA, 700-2 RA for PBH 2000 SRE, 2000 RE	2 605 438 389 2 605 438 328 2 605 438 377 2 605 438 286 2 605 438 338 2 605 438 099 2 605 438 199 2 605 438 602
45	Drill suction nozzle for connecting to dust extractor hoses with Ø of 35 mm	2 607 002 526

### Attachments

Pic.	Description	Part no.
46	Machine vices with quick adjustment MS 65, jaw opening 65 mm MS 80, jaw opening 80 mm	2 608 030 053 2 608 030 055
47	Bench stand for bench-mounted use of drills with spindle collar Ø of 43 mm. Can be swivelled and turned through 360° horizontally and vertically	2 608 120 004
48	Drill Stand DP 500 For all drills with spindle collar Ø of 43 mm. Fast setting due to adjustable clamp lever; variable adjustment	2 608 180 009
49	Flexible drives The drill is to be secured firmly in place with the bench stand no. 87 (2 608 120 004). Length 1250 mm, speed up to 3500 rpm, weight 0.9 kg. For drill chucks up to 6 mm. Comes complete with: 1 locking pin, 1 drill chuck.  Highly flexible design Replacement chuck for flexible drive	2 609 200 195  2 609 200 196 2 608 572 097
50	Quick-action clamp For Drill Stand DP 500. Ideal for fast, easy fixing of workpieces, such as metal plates, but also pipes and profiles. Easy to operate with one hand.	2 608 180 010
51	Drill Bit Sharpener S 41 suitable for steel and HSS twist drill bits or flute drill bits with 2.5–10 mm Ø and cutting edge angle of approx. 110° to 116°. Accessories: Spare abrasive wheel	2 607 990 050  2 608 600 029
52	Water pump General purpose pumps for drills with impact-resistant plastic housing; self-extracting and self-cooling. Drive via chuck.  1/2" hose connection Max. pumping capacity 1500 l/h, delivery height >18 m, inlet height 3 m Max. pumping capacity 2000 l/h, delivery height >40 m, inlet height 4 m	2 609 200 250 2 609 200 251
	Water pump holder for water pump 2 609 200 251	2 609 200 253
	Replacement drive wheel for all water pumps	2 609 200 254
	Inlet filter for water pump for 1/2" and 3/4" hoses	2 609 200 255
<b>For safe handling and care</b>		
not illus.	Ear plugs Insulation level 30 dBA	2 607 990 044

