



Service unit combination FRC-1/4-DB-7-MINI-KC

Part number: 8002801

FESTO

Output pressure max. 7 bar, with pressure gauge, 40 µm filtration grade.



Data sheet

Feature	Value
Size	Mini
Width	158 mm
Exhaust-air function	not throttleable
Series	DB
Actuator lock	Padlock (optional) Rotary knob with lock
Assembly position	Vertical +/- 5°
Type of actuation	manual
Condensate drain	manual rotary
Design structure	On-off valve/filter regulator/distributor module/lubricator
Max. condensate volume	13 ml
Grade of filtration	40 µm
Controller function	Output pressure constant with secondary exhaust with return flow Without primary pressure compensation
Pressure gauge	with pressure gauge
Operating pressure	1.5 ... 10 bar
Pressure regulation range	0.5 ... 7 bar
Max. pressure hysteresis	0.5 bar
Max. standard flow rate	2,400 l/min
Standard nominal flow rate	400 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:4]
Note on operating and pilot medium	Lubricated operation not possible
Approved oils	Festo special oil in 1-litre containers Order code: 152 811 OFSW-32 ARAL Vitam GF 32 ESSO Nuto H 32 MOBIL DTE 24 SHELL Tellus Oil DO 32 Range of viscosity 32mm ² /s at 40°C ISO class VG 32 to ISO 3448
Corrosion resistance classification CRC	1 - Low corrosion stress
Storage temperature	-5 ... 50 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:9:-]
Medium temperature	-5 ... 50 °C
Oil viscosity	ISO VG 32
Ambient temperature	-5 ... 50 °C
Product weight	360 g
Mounting type	Optional Line installation with through hole With mounting bracket
Pressure gauge connection	G1/8

Feature	Value
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/4
Materials note	Conforms to RoHS
Material seals	NBR
Material on-off valve seals	FPM
Material rotary knob	POM
Material filter	PE
Material housing	PA-reinforced
Material Piston slide	POM
Material bowl	PC