

Data Sheet

Product: Noga Camera Arms



The Noga Camera Arm range utilise a 3 jointed fully articulated holding system which provides safe and easy positioning of photographic and cine bolt on accessories such as lights and monitors

The heart of the device is a single central locking knob which locks all 3 joints simultaneously

The central locking mechanism has a smooth action and can be tightened to hold the fitted accessory firm enough to support it but to also allow for exact positioning before final tightening

The unit to be mounted is screwed onto the top of the arm and is securely locked using the knurled locking ring

The DG Series is the most popular size in the Camera Arm family and provides a unit suitable for most general applications

The NF Series is the smallest in the Camera Arm family and provides a compact unit suitable for small and lightweight applications

The MG Series is the largest size in the Camera Arm family and provides a unit suitable for heavy duty applications

RS Code	Manufact Code	Top Arm Length mm	Bottom Arm Length mm	Total Arm Length mm	Top Male Thread mm	Bottom Male Thread mm	Max Load Weight Fully Extended	Arm Weight Kilos	Arm Material
7857850	DG-11043	101	110	211	1/4"-20	3/8"-16	4K	0.304K	Aluminium
7857856	DG-1105	101	110	211	1/4"-20	1/4"-20	4K	0.304K	Aluminium
7857853	NF-1104	56	51	107	1/4"-20	3/8"-16	2.7K	0.315K	Steel
7857844	NF-1105	56	51	107	1/4"-20	1/4"-20	2.7K	0.315K	Steel
7857869	MG-1106	113	133.5	246.5	1/4"-20	3/8"-16	6.8K	0.517K	Aluminium

Examples:

