




Part Number : [5050702222](#)

Product Description : SlimStack Board-to-Board Plug, 0.35mm Pitch, SSB RP Series, 0.60 or 0.70mm Mated Height, 2.00mm Mated Width, 22 Circuits, Armor Nail, 0.15mm Fitting Nail Width

Series Number : 505070

Status : Active

Product Category : Board-to-Board Connectors



Documents & Resources

Drawings

[5050702222_sd.pdf](#)

3D Models and Design Files

[5050702222.dxf](#)

[5050702222.pdf](#)

[5050702222_stp.zip](#)

Specifications

[5050660000-A06.pdf](#)

[5050709200-203.pdf](#)

[5050660000-014.pdf](#)

[5052700002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	505070
Description	SlimStack Board-to-Board Plug, 0.35mm Pitch, SSB RP Series, 0.60 or 0.70mm Mated Height, 2.00mm Mated Width, 22 Circuits, Armor Nail, 0.15mm Fitting Nail Width
Series Name	0.35, SSB RP
Application	Board-to-Board
Component Type	PCB Header
Product Name	SlimStack
UPC	191128261661

Electrical

Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No

Mated Height	0.60mm, 0.70mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	6.031/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.35mm
Pitch - Termination Interface	0.35mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.35mm Pitch SlimStack Board-to-Board Receptacles	<u>505066</u>
0.35mm Pitch SlimStack Board-to-Board Receptacles	<u>505270</u>