



M12/M8 Connectivity

Food & Beverage Range

M12, 4 pole, 0°, male to M8, 4 pole, 0°, female connector lead for the Food & Beverage Industry

Stock No's 154-7766, 154-7767



Primary Features

V4A Stainless steel hexagonal nut means there are minimum traps for debris to collect

IP65, IP68 when inserted and tightened

CSA and Ecolab approved


Available in lengths:


2 Metres (RS 154-7766)

5 Metres (RS 154-7767)









Male

Female









154-7766, 154-7767
211
1 (PVC)
UL (AWM-Style 2464/1731), CSA
34,76
Cu wire, bare
max. 79 Ohm/km (20 °C)
0.15 mm
14 × 0.15 mm (multi-strand wire class 5)
4 × 0.25 mm²
similar to AWG 24
PVC
CFC-, cadmium-, silicone- and lead-free
45 ±5 D
1.25 mm ±5%
br, bk, bl, wh
4 wires twisted
no
PVC
CFC-, cadmium-, silicone- and lead-free
85 ±5 A
4.8 mm ±5%
gray
good resistance to oil, gasoline and chemicals
UL 300 V AC
2000 V AC
to DIN VDE 0298-4
-30+80 °C
-5+80 °C
5 × outer Ø
10 × outer Ø





Cable continued

154-7766, 154-7767

No./diameter of wires	4 × 0.25 mm ²
Wire isolation	PVC (br, wh, bl, bk)
Jacket Color	gray
Material (jacket)	PVC (UL/CSA)

Technical Data

recilincal Data	
Operating voltage	max. 30 V AC/DC
Rated surge voltage	0.8 kV
Operating current per contact	max. 4 A
No. of poles	4
Material group	IEC 60664-1, category I
Locking of ports	Screw thread M8 \times 1 mm (recommended torque 0.4 Nm) self-securing
Compression gland	M8 (SW9), M12 (SW13)
Protection	IP65, IP66K, IP67, IP68 inserted and tightened (EN 60529)
Locking material	Stainless Steel 1.4404 (V4A)
Material	PUR
suitable for corrugated tube (internal Ø)	M12 (10 mm); M8 (6.5 mm)
Mounting method	inserted, tightened
Pollution Degree	3
Stripping length (jacket)	20 mm
Temperature range	-25+85 °C, depending on cable quality