



 PRODUCT-DETAILS

OT250ERRR6TZ

OT250ERRR6TZ Safety switch



General Information

Extended Product Type	OT250ERRR6TZ
Product ID	1SCA102365R1001
EAN	6417019371412
Catalog Description	OT250ERRR6TZ Safety switch

Long Description	<p>Safety switch, 6-p. 415V AC23 250A, 132kW. Mounted auxiliary contact: 4NO2NC. Stainless steel enclosure. IP65. StainlessSteel Pistol handle. Interlocked cover. Defeatable interlocking. The enclosure and handle of the OT series is made of rigid acid proof steel, class AISI316L. The enclosure has a hinged door, with door lock. The cover is interlocked, and can not be opened when switch is on. The interlock function can be defeated for thermographing. The cover has also a gas pressure releaf function, to protect the user in case of internal arc. Suitable for outdoor and indoor use. The cable entries holes are prepared for cable flanges. The cable flanges (KOT61007 or KOT62296 (for EMC)) and the covers for the holes (KOT61008), have to be bought separately. The switch can be used in EMC applications, if EMC ring flanges are used. PE terminals and auxiliary contacts are included.</p>
------------------	--

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340008M0004

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country or Territory of Origin	Finland

Dimensions

Product Net Width	800 mm
Product Net Height	800 mm
Product Net Depth / Length	230 mm
Product Net Weight	42.14 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	815 mm
Package Level 1 Depth / Length	910 mm
Package Level 1 Height	325 mm
Package Level 1 Gross Weight	46 kg
Package Level 1 EAN	6417019371412

Technical

Cable Entry Position	Top/Bottom
Cable Outlets Per Side	8xring-flange+ø25.5mm / 8xring-flange+ø25.5mm
Color	Stainless
Connecting Capacity Main Circuit	Hole Diameter 8 mm Screw Clamp / PE Terminal 8pc,25 ... 120 mm ²
Conventional Thermal Current (I _{the})	Fully Enclosed 250 A

Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Stainless steel
Handle Color	Stainless Steel
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted Auxiliary Contacts	4 NO, 2 NC
Mounted Auxiliary Contacts	4 NO, 2 NC
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	4
Number of Poles	6P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Rated Conditional Short-Circuit Current (I_{nc})	40.5 kA
Rated Insulation Voltage (U_i)	750 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 132 kW (500 V) 160 kW (690 V) 200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(1000 V AC) 30 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 8 kA
Recommended Screw Driver	Main Circuit M8
Special Functions	EMC
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 22 N·m

Technical UL/CSA

Recommended Screw Driver	Main Circuit M8
Tightening Torque	Main Circuit 22 N·m

Certificates and Declarations

Declaration of Conformity - CE	1SCC340025D2704
--------------------------------	-----------------

External Classifications and Standards

Object Classification	Q
-----------------------	---

Code	
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
E-Number (Finland)	3642124

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

