

AGILA LIGHT

1470PA0075S50 10X33,5



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila light
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.73 in
Overall weight	0.47 lb

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material	Steel sheet, light
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.98 in
Swivel radius	2.46 in
Swivel interference	4.92 in
Dome diameter	1.61 in

FITTING

Fitting type	Socket head cap screw, loose fitted
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.