

# Product datasheet

Specifications



## Acti9 - IH - mechanical time switch - 24 h - without memory

Local distributor code:

399370852

CCT16364

EAN Code: 3606480179570

### Main

range of product	Acti9
Product name	Acti9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

### Complementary

Device application	Building
Load type	230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1100 W 230 V AC fluocompact lamp 600 VA Parallel-corrected fluorescent tube 2 x electronic ballast 40 W 12 µF Compact fluorescent lampelectronic ballast 25 W LED lamp < 2 W 20 W LED lamp > 2 W 180 W
Cycle duration	24 h
Maximum number of switchings	48 on - 48 off
Minimum interval duration	15 min
Type of setting	Manual time changeover
Power consumption in W	0.5 W
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC at 50 Hz
Mounting support	DIN rail
9 mm pitches	6
Colour tint	White (RAL 9003)
Connections - terminals	Screwless terminals
Clamping connection capacity	2 x 0.5...2 .5 mm <sup>2</sup>
Width	54 mm
Height	90 mm
Depth	66 mm
Net weight	0.135 kg
Standards	EN 60730-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

---

Ambient air temperature for operation	-20...55 °C
IP degree of protection	IP20 conforming to EN 60529

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	6.500 cm
------------------	----------

---

Package 1 Width	7.700 cm
-----------------	----------

---

Package 1 Length	10.400 cm
------------------	-----------

---

Package 1 Weight	147.000 g
------------------	-----------

---

Unit Type of Package 2	S03
------------------------	-----

---

Number of Units in Package 2	36
------------------------------	----

---

Package 2 Height	30.000 cm
------------------	-----------

---

Package 2 Width	30.000 cm
-----------------	-----------

---

Package 2 Length	40.000 cm
------------------	-----------

---

Package 2 Weight	5.787 kg
------------------	----------

## Logistical informations

---

Country of origin	DE
-------------------	----

## Contractual warranty

---

Warranty (in months)	18
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better



#### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant

SCIP Number

90215406-b6bf-44f8-b463-8540d32a6f6b

REACH Regulation

[REACH Declaration](#)

### Use Longer



#### Lifetime extension

Repair

No

### Use Again



#### Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins