


**KEMET Part Number: PEH200PD4470MU2**  
(A351GK472M100A)

PEH200, Aluminum Electrolytic, 4,700 uF, 20%, 100 VDC, -40/+85°C



General Information	
<b>Supplier:</b>	KEMET
<b>Series:</b>	PEH200
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Description:</b>	Screw Terminal, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>AEC-Q200:</b>	No
<b>Notes:</b>	Dimensions D And L Include Sleevings. MS (MxS) = M8x12
<b>Shelf Life:</b>	156 Weeks

Dimensions	
<b>D</b>	36.6mm +/-1mm
<b>L</b>	94.5mm +/-1mm
<b>T</b>	4.4mm NOM
<b>S</b>	13mm +/-0.5mm
<b>F</b>	8mm +/-0.5mm
<b>DT</b>	8mm NOM
<b>LT</b>	101.9mm +/-1mm

Specifications	
<b>Capacitance:</b>	4,700 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	100 VDC
<b>Temperature Range:</b>	-40/+85°C
<b>Rated Temperature:</b>	85°C
<b>Life:</b>	10000 Hrs (Rated Voltage And Ripple Current At 85C)
<b>Resistance:</b>	31 mOhms (100Hz 20C), 21 mOhms (100kHz 20C)
<b>Ripple Current:</b>	10.3 Amps (100Hz 85C), 28.9 Amps (10kHz 50C), 21.1 Amps (10kHz 40C)
<b>Leakage Current:</b>	5410 uA (5min 20°C)
<b>Inductance:</b>	12 nH (ESL)

Packaging Specifications	
<b>Weight:</b>	130 g
<b>Sleevings:</b>	Yes
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	42