

# LE4K065P7

enclosed DOL non reversing starter TeSys -  
LE4-K - 6 A - coil 230 V AC



## Main

Range of product	TeSys
Device short name	LE4K
Product or component type	Enclosed DOL starter
Contactor application	Motor control
Poles description	3P
Motor starter type	Non reversing
Motor power kW	2.2 kW at 415 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz 1.5 kW at 220/230 V AC 50/60 Hz 3 kW at 440 V AC 50/60 Hz
Utilisation category	AC-3
[Uc] control circuit voltage	230 V AC 50/60 Hz
Protection type	Fuse 10 A 10 x 38 mm aM
[Ith] conventional free air thermal current	6 A
Control type	1 stop/reset button 0 red 1 start button I green
Enclosure material	Polycarbonate

## Complementary

Cable entry	2 x 13 mm PG at bottom 2 x 13 mm PG at top 2 x 16 mm PG at bottom 2 x 16 mm PG at top 4 x 20 mm ISO at bottom 4 x 20 mm ISO at top
Width	175 mm
Height	165 mm
Depth	146 mm
Product weight	1.45 kg

## Environment

IP degree of protection	IP659
Standards	EN 60947 IEC 60439-1 IEC 60947-4-1 VDE 0660-102
Ambient air temperature for operation	-5...40 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.