



Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 2

Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **.5 mm [.019 in]**

Connector System: **Wire-to-Wire**

Centerline (Pitch): **1.8 mm [.07 in]**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	.5mm
--------------	------



Contact Type	Receptacle
Mating Tab Width	.5 mm[.019 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	1.8 mm[.07 in]

Dimensions

Product Width	15.95 mm[.627 in]
Product Length	5.25 mm[.206 in]
Connector Height	4.9 mm[.192 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free








Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2324309-3 3-PORT MATENET FRAME, UTP, COD C	 TE Part # 2324309-9 3-PORT MATENET FRAME, UTP, COD Z	 TE Part # 2307961-3 2-PORT MATENET FRAME,STP, COD C	 TE Part # 2357268-1 RING TONGUE TRMNL,STP 0.35MM TERMINAL
 TE Part # 2327450-1 5PORT,MATENET,REC HSG,COD A, SUBASSM	 TE Part # 2302510-1 1-PORT MATENET FRAME,STP, COD A	 TE Part # 1802105-5 1PORT,MATENET,REC HSG,SLD,COD E,UTP,ASSY	 TE Part # 2334013-7 2X3 PORT,MATENET,FRAME housing, COD J
 TE Part # 2334013-3 2X3 PORT,MATENET,FRAME housing, COD C	 TE Part # 1802105-7 1PORT,MATENET,REC HSG,SLD,COD J,UTP,ASSY	 TE Part # 2334013-2 2X3 PORT,MATENET,FRAME housing, COD B	 TE Part # 2334013-1 6 PORT,MATENET,HDR HSG,COD A





TE Part # 2324309-1
3-PORT MATENET FRAME, UTP, COD A



TE Part # 2305974-9
2-PORT MATENET FRAME, UTP, COD Z



TE Part # 2305974-2
2-PORT MATENET FRAME, UTP, COD B



TE Part # 2302452-2
MATENET, FIXATION ELEMENT



TE Part # 9-2348776-1
HD MATenet 3+0 REC HSG ASSY, GRP E



TE Part # 2357266-1
RING TONGUE TRMNL, STP 0.35MM TERMINAL



TE Part # 2349433-1
1PORT, TOP LATCH, MATENET, REC HSG, COD A



TE Part # 1802105-4
1PORT, MATENET, REC HSG, SLD, COD D, UTP, ASSY

Also in the Series

MATenet




Automotive Connector Caps & Covers (5)




Automotive Housings(1)



Connector Seals & Cavity Plugs(6)



Data Connectivity Headers(9)



Data Connectivity Housings(29)

Customers Also Bought



TE Part #2278882-1
43 WAY SOCKET2



TE Part #1802110-1
COVER, MATENET SEALED PROTECTION, UTP



TE Part #2141868-1
MCON 1.2 LL TAB SWS SN



TE Part #2302452-3
MATENET, FIXATION ELEMENT



Documents

- Product Drawings
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English
- MATENET, FEMALE INSERT MODUL, BLACK
- English



English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

[MATENET, FEMALE INSERT MODUL, BLACK](#)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2302450-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2302450-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2302450-1_B.3d_stp.zip](#)

English

2302450-1

2 Position Housing, Housing for Female Terminals, Wire-to-Wire, 1.8 mm [.07 in]
Centerline, Black, Signal, Cable Mount (Free-Hanging), MATEnet



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English