




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	14.99 mm[.59 in]
Compatible Insulation Diameter Range	2.3 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.51 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	15000
Packaging Method	Strip/Reel

Other

Line	FASTON .187
------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 62137-1 187 FASTON REC 20-16 BR	 TE Part # 62137-2 187 FASTON REC 20-16 TPBR	 TE Part # 42452-1 187 FASTON REC 20-16 AWG BR	 TE Part # 62865-1 187 FASTON REC 20-16 AWG TPBR
 TE Part # 61758-1 187 FASTON REC 20-16 AWG BR	 TE Part # 7-160433-1 187 FASTON REC 20-15 AWG BR	 TE Part # 61758-2 187 FASTON REC 20-16 AWG TPBR	 TE Part # 63556-2 187 FASTON REC 20-16 AWG TPBR
 TE Part # 42452-2 187 FASTON REC 20-16 AWG TPBR	 TE Part # 42452-5 187 FASTON REC 20-16 AWG TPBZ		

Also in the Series | **FASTON 187**



Crimp Terminal Housings(40)



Insertion & Extraction Tools(1)



Insulation Boots & Sleeves(1)



Joints & Splices(1)



PCB Terminals(42)



Quick Disconnects(205)



Splices(1)


Customers Also Bought



TE Part #1-1971773-2
PTL 1X2 PLUG HSG STD TEMP KEY A NAT



TE Part #2321927-4
FRONT TPA RECEPTACLE, 4 POS NAT




TE Part #1376396-1
5MM POWER KEY D/L PLATE GREEN




TE Part #2321918-4
PLUG HOUSING SDL2.5 WATERPROOF 4PIN




TE Part #3-640470-4
04P MTA100 CONN ASSY ON TAPE




TE Part #171370-5
CLUSTER BLOCK HSG PBT



TE Part #1376389-1
5MM POWER KEY 3P PLUG HSG NUT



TE Part #170221-3
TAB WITH LANCE FOR M.I.C.



TE Part #925014
2 P FF 110(2.8 MM) HOUSING RECEPTACLE

Documents



Product Drawings

187 FASTON,REC.,20-16 AWG,BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_157440-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_157440-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_157440-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

.110,.187 & 250 Series FASTON Terminals

English

Product Specification

English