



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2-2176341-2  
CRGCQ 0805 560R 1%

TE Part #CAT-D9934-A66A  
Receptacle and Tab Housing: 2.5 mm Pitch, 250V

TE Part #215309-2  
2X2P HV100 REC CON. TE, 8.5MM

TE Part #825440-4  
MOD 2 PINHDR 2X04P.

TE Part #2-2176345-4  
CRGCQ 1210 820R 1%

TE Part #5-103634-1  
02 MTE HDR SRRA LATCH.100CL LF

TE Part #9-1614353-1  
RN 0603 49R9 0.1% 10PPM CUT LENGTH

TE Part #4-1393479-5  
V23529A1223C225=SUB D STIFTLEI

TE Part #3-1393479-8  
V23529A1223B209=SUB D FEDERLEI

Documents

Product Drawings

V23529A1223C215=SUB D STIFTLEI

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1393479-4\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393479-4\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393479-4\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.