



Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	PowerPact B Compact NSXm
Voltage release type	Shunt trip
[Uc] control circuit voltage	380...415 V AC 440...480 V AC

Complementary

Control signal type	Impulse Maintained
Impulse duration	≥ 20 ms
Threshold tripping voltage	0.7 Un - during opening time
Mounting mode	Clip-on
Response time	< 50 ms
Auxiliary connection terminal	Spring
Wire stripping length	8 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold