

Installation

- 1. Remove the two screws holding the diffuser to gain access to the interior.
- Press the two tabs to release the LED tray to access the mains input terminal. This is hinged so the LED tray remains attached to the body.
- 3. Cable entry is available through rear, top and bottom or both ends. Ensure appropriate grommets or compression couplings are used to maintain the IP65 rating where required.
- 4. Connect the mains input supply as indicated on the left as per the required operation.
- 5. Connect the emergency battery leads to the circuit board where indicated.
- 6. Relocate the LED tray, ensuring it is secured using the tabs.
- 7. Refit the diffuser ensuring there is a good seal to maintain the IP65 rating.
- 8. Switch on mains supply and test for operation(allow 24hrs for batteries to charge).
- 9. Fit the legend on the front of the diffuser to suit the application from the four choices indicated on the right which are included.
- 10. Familiarise yourself with the enclosed emergency fittings test record sheet and ensure it is completed as required and left with the end user.