




**Part Number :** [732870773](#)

**Product Description :** Chip Termination, DC-10 GHz,  
5 Watts

**Series Number :** 73287

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[732870773\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73287
Description	Chip Termination, DC-10 GHz, 5 Watts
Application	RF
Keyword	Termination, Terminations
Product Name	Termination
Style	Chip Termination
Type	N/A
UPC	198930382409

### Electrical

Average Power Max (Watts)	5
Frequency	DC-10
Impedance	50Ω
VSWR (max)	1.25:1

### Physical

Ceramic Substrate	Beryllium Oxide
Gender	N/A
Height	0.254mm
Keying to Mating Part	N/A
Length	1.27mm
Material - Contact	Tin Lead Solder
Orientation	N/A
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A

Width	1.27mm
Wire/Cable Type	N/A

---

This document was generated on May 08, 2026