

Features

- Waterproof IP67 rating guarantees protection against extended immersion under higher pressures
- Voltage rating of 60V AC/32V DC
- Current rating of 5A
- Gold-plated brass contacts for corrosion resistance
- Threaded mating type
- Operating temperature range from -25°C to 80°C
- Nickel plated brass shell
- Conforms to standards IEC 61076-2-106

RS PRO Female M16 8 Pin Connector

RS Stock No.: 0124630



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The 8 pin female M16 metal front mount socket connector had been widely used for automotive and sensor application, it's unshielded.

General Specifications

Number of Contacts	8
Shielding	unshielded
Housing Material	Brass
Contact Material	Phosphor copper
Contact Plating	Gold
Pole Format	8 pin
Contact Gender	Female
Mating Type	Threaded
Body Orientation	Straight
Mating Cycles	500
Cable limits	/
Typical conductor size	20AWG
Application	Sensor, automation

Plug/Socket	Socket
Current Rating	5A
Voltage Rating	60V AC/32V DC
Insulation Resistance	≥100MΩ

Mechanical Specifications

Connector Size	Standard
Termination Method	Solder
Mounting Type	Panel mount
Panel Cut-Out	φ18.1mm*17.1mm
Contact Diameter	20AWG

Operation Environment Specifications

Operating Temperature	-25℃ to 80℃
-----------------------	-------------

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE, RoHS, REACH, IP67
---------------------------	-----------------------