



**Part Number :** [731740910](#)

**Product Description :** DIN 1.0/2.3 Plug, Straight, Crimp, Belden 1855A Cable, Push-pull Coupling, Brass Body, Nickel (Ni) Plated, Tray, 75 Ohms

**Series Number :** 73174

**Status :** Active

**Product Category :** RF / Coaxial Connectors

---

## Documents & Resources

### Drawings

[731740910 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73174
Description	DIN 1.0/2.3 Plug, Straight, Crimp, Belden 1855A Cable, Push-pull Coupling, Brass Body, Nickel (Ni) Plated, Tray, 75 Ohms
Product Name	DIN 1.0/2.3
Style	Cable
Type	Subminiature
UPC	884982298149

### Electrical

Frequency	3 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 250 Vrms@Sea Level

### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	4.243/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	Belden 1855A

### **Solder Process Data**

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Aug 04, 2025