

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 3 mm ... 6.5 mm, shielding: no, connecting thread: Pg7, color: silver-gray RAL 7001

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

Item number	1411140
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DCX
Product key	AF7DCX
Catalog page	Page 687 (C-2-2019)
GTIN	4046356922722
Weight per piece (including packing)	3.66 g
Weight per piece (excluding packing)	3.66 g
Customs tariff number	39269097
Country of origin	TR

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

## Technical data


### Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---

### Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BS-01
Shielded	no

### Dimensions

Dimensional drawing	
Length	32 mm
Length of the connecting thread	8 mm
Hole diameter	12.6 mm ... 12.7 mm
Wrench size, union nut	15 mm
Wrench size, support	15 mm
Hexagon angular dimension	17.1 mm
Thread type connection side	Pg7

### Connection data

Tightening torque	2 Nm $\pm$ 0.5 Nm (Cap nut) 1 Nm (Support sleeve)
-------------------	--

### Material specifications

Color	silver grey (RAL 7001)
Material Housing	PA (Housing)
Flammability rating according to UL 94	V2
Seal material Cable seal	CR
Material for screw connection	PA

### Cable/line

External cable diameter Cable 1	3 mm ... 6.5 mm
External cable diameter	4 mm ... 6 mm (for UL 514 B)
Halogen-free	no

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Enclosure rating (NEMA)	1
	4
	4X
	12
	13
Ambient temperature (operation)	-40 °C ... 100 °C (static)

# G-INS-PG7-S68N-PNES-GY - Cable gland


1411140

<https://www.phoenixcontact.com/gb/products/1411140>



## Drawings

Dimensional drawing



Dimensional drawing

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1411140>

**DNV**

Approval ID: TAE00003WX



**CSA**

Approval ID: 115116



**UL Recognized**

Approval ID: E199260

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

## Classifications

### ECLASS

ECLASS-13.0	27140801
-------------	----------

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# G-INS-PG7-S68N-PNES-GY - Cable gland



1411140

<https://www.phoenixcontact.com/gb/products/1411140>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)