

Wiha MagicRing® hexagon L-key.

Securely holds hexagon bolts in place in any position.

For Allen screws (inch).



369R Zoll Ball end hex L-key, long.
With MagicRing®. Inch sizes.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Based on ASME B18.3.
 Application: Insert hex inch screws into and remove from boreholes, especially in difficult to access areas.
 Extra: MagicRing® made from spring steel holds all standard screws tight at various angles (available from 1/8").
 The ball end enables the user to work at angles up to 25°.

Order-No.	●	↔	!↔	mm	↔
29471 7	0.05	72	13	1.27	10
29472 4	1/16	80	15	1.59	10
29474 8	5/64	88	18	1.98	10
29473 1	3/32	101	20	2.38	10
29475 5	7/64	111	21	2.78	10
24302 9	1/8	121	23	3.17	10
24304 3	9/64	136	27	3.57	10
24303 6	5/32	148	29	3.96	10
24305 0	3/16	163	33	4.76	10
24306 7	7/32	176	36	5.55	10
24307 4	1/4	191	38	6.35	10
24308 1	5/16	210	43	7.93	10
24341 8	3/8	232	50	9.52	10

For Allen screws (inch).



369R SZ13 Ball end hex L-key set in ProStar.
With MagicRing®, chrome-plated, 13 pcs.
Inch sizes.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Based on ASME B18.3.
 Application: Insert hex inch screws into and remove from boreholes, especially in difficult to access areas.
 Extra: Space saving ProStar allows the easy removal of each key without moving any others.
 MagicRing® made from spring steel holds all standard screws tight at various angles (available from 1/8").
 The ball end enables the user to work at angles up to 25°.

Order-No.	↔
24190 2	369R SZ13 5
●	369 Zoll C 0.05 1/16 5/64 3/32 7/64
●	369R Zoll 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8

SB 369R SZ13 Ball end hex L-key set in ProStar.
With MagicRing®, chrome-plated, 13 pcs.
Inch sizes.
Blister packed.

Order-No.	↔
24850 5	SB 369R SZ13 5
●	369 Zoll C 0.05 1/16 5/64 3/32 7/64
●	369R Zoll 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8

Wiha hex L-keys (metric).

For Allen screws (metric).



369 Ball end hex L-key, long.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Based on ISO 2936L.
 Application: Especially for screws that are difficult to access.
 Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	●	↔	!↔	↔
01392 9	1.5	91	15	10
01393 6	2	101	18	10
01395 0	2.5	113	20	10
01396 7	3	128	23	10
01398 1	4	142	29	10
01400 1	5	163	33	10
01402 5	6	184	38	10
07922 2	7	195	39	5
01404 9	8	206	44	10
01406 3	10	231	50	5
01408 7	12	259	57	5

SB 369 Ball end hex L-key, long.
Blister packed.

Order-No.	●	↔	!↔	↔
08161 4	1.5	91	15	10
08162 1	2	101	18	10
08163 8	2.5	113	20	10
08164 5	3	128	23	10
08165 2	4	142	29	10
08166 9	5	163	33	10
08167 6	6	184	38	10
08168 3	8	206	44	5
08169 0	10	231	50	5
08170 6	12	259	57	5

For Allen screws (metric).



369 S9 Ball end hex L-key set in ProStar.
Chrome-plated, 9 pcs.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Standards: Based on ISO 2936L.
 Application: Especially for screws that are difficult to access.
 Extra: Space saving ProStar allows the easy removal of each key without moving any others.
 The ball end enables the user to work at angles up to 25°.

Order-No.	↔
07185 1	369 S9 5
●	369 1.5 2 2.5 3 4 5 6 8 10

SB 369 S9 Ball end hex L-key set in ProStar.
Chrome-plated, 9 pcs.
Blister packed.

Order-No.	↔
07192 9	SB 369 S9 5
●	369 1.5 2 2.5 3 4 5 6 8 10



369 SVH1 Display ball end hex L-key sets.
 Chrome-plated, in ProStar, 9 pcs.
 Carton display with 10 pieces.

Order-No.	Content	●	↔
07194 3	10 x 369 S9	1.5 - 10	1

Wiha Info



Wiha MagicRing®:
 spring steel ring
 reliably holds hex screws
 in place.

Wiha hex L-keys (metric).

For Allen screws (metric).



369 H9 Ball end hex L-key set in holder.
Chrome-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Thanks to its compact dimensions, this holder fits easily into every ruler pocket.
Popular key sizes kept in a well-organised holder.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 H9	5
01418 6	369	1.5 2 2.5 3 4 5 6 8 10

SB 369 H9 Ball end hex L-key set in holder.
Chrome-plated, 9 pcs.
Blister packed.

Order-No.	SB 369 H9	5
02292 1	369	1.5 2 2.5 3 4 5 6 8 10



369 H7 Ball end hex L-key set in holder.
Chrome-plated, 7 pcs.


Blade: Chrome-vanadium steel, through hardened, chrome-plated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 H7	5
01416 2	369	1.5 2 2.5 3 4 5 6

SB 369 H7 Ball end hex L-key set in holder.
Chrome-plated, 7 pcs.
Blister packed.

Order-No.	SB 369 H7	5
03723 9	369	1.5 2 2.5 3 4 5 6

For Allen screws (metric).



369 B8 Ball end hex L-key set in sliding box.
Chrome-plated, 8 pcs.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Large, impact resistant sliding box.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 B8	5
01410 0	369	2 2.5 3 4 5 6 8 10



369B Ball end hex L-key, long.
Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	369B	10
01391 2	1.3	74 14
05638 4	1.5	91 15
03868 7	2	101 18
03869 4	2.5	113 20
03870 0	3	128 23
03871 7	4	142 29
03872 4	5	163 33
03873 1	6	184 38
03874 8	8	206 44
03875 5	10	231 50
03876 2	12	259 57

For Allen screws (metric).



369 S9B Ball end hex L-key set in ProStar.
Manganese-phosphated, 9 pcs.
Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Space saving ProStar allows the easy removal of each key without moving any others.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 S9B	5
07186 8	369B	1.5 2 2.5 3 4 5 6 8 10

SB 369 S9B Ball end hex L-key set in ProStar.
Manganese-phosphated, 9 pcs.
Blister packed.


Order-No.	SB 369 S9B	5
07193 6	369B	1.5 2 2.5 3 4 5 6 8 10



369 SVH1B Display ball end hex L-key sets.
Manganese-phosphated, in ProStar, 9 pcs.
Carton display with 10 pieces.

Order-No.	Content	1
07195 0	10 x 369 S9B	1.5 - 10

For Allen screws (metric).



369 H9B Ball end hex L-key set in holder.
Manganese-phosphated, 9 pcs.
Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 H9B	5
03879 3	369B	1.5 2 2.5 3 4 5 6 8 10

SB 369 H9B Ball end hex L-key set in holder.
Manganese-phosphated, 9 pcs.
Blister packed.

Order-No.	SB 369 H9B	5
03992 9	369B	1.5 2 2.5 3 4 5 6 8 10



NEW
369 H7B Ball end hex L-key set in holder.
Manganese-phosphated, 7 pcs.
Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.
The ball end enables the user to work at angles up to 25°.

Order-No.	369 H7B	5
03878 6	369B	1.5 2 2.5 3 4 5 6

NEW
SB 369 H7B Ball end hex L-key set in holder.
Manganese-phosphated, 7 pcs.
Blister packed.

Order-No.	SB 369 H7B	5
03991 2	369B	1.5 2 2.5 3 4 5 6

Wiha hex L-keys (metric).

For Allen screws (metric).



352 Hex L-key, long.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ISO 2936L.

Order-No.	Blade	Length	Width	Height
01201 4	1.5	91	15	10
01202 1	2	101	18	10
01203 8	2.5	113	20	10
01204 5	3	128	23	10
01206 9	4	142	29	10
01207 6	5	163	33	10
01208 3	6	184	38	10
01209 0	7	194	41	5
01210 6	8	206	44	10
01211 3	10	231	50	5
01212 0	12	259	57	5
01213 7	14	291	70	5
01214 4	17	333	80	5
01215 1	19	375	89	5



352 S9 Hex L-key set in ProStar.

Nickel-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ISO 2936L.
Extra: Space saving ProStar allows the easy removal of each key without moving any others.

Order-No.	Blade	Length	Width	Height
07181 3	352 S9			5
352	1.5 2 2.5 3 4 5 6 8 10			

SB 352 S9 Hex L-key set in ProStar.

Nickel-plated, 9 pcs.
Blister packed.

Order-No.	Blade	Length	Width	Height
07190 5	SB 352 S9			5
352	1.5 2 2.5 3 4 5 6 8 10			

For Allen screws (metric).



352 H9 Hex L-key set in holder.

Nickel-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ISO 2936L.
Extra: Thanks to its compact dimensions, this holder fits easily into every ruler pocket.
Popular key sizes kept in a well-organised holder.

Order-No.	Blade	Length	Width	Height
01222 9	352 H9			5
352	1.5 2 2.5 3 4 5 6 8 10			



352 H7 Hex L-key set in holder.

Nickel-plated, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ISO 2936L.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	Blade	Length	Width	Height
01220 5	352 H7			5
352	1.5 2 2.5 3 4 5 6			



352 B8 Hex L-key set in sliding box.

Nickel-plated, 8 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ISO 2936L.
Extra: Large, impact resistant sliding box.

Order-No.	Blade	Length	Width	Height
01216 8	352 B8			5
352	2 2.5 3 4 5 6 8 10			

For Allen screws (metric).




352B Hex L-key, long.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.

Order-No.	Blade	Length	Width	Height
06358 0	0.7	67	6	5
06359 7	0.9	70	9	5
06360 3	1.3	80	13	5
06059 6	1.5	91	15	5
06361 0	2	101	18	5
06362 7	2.5	113	20	5
06363 4	3	128	23	5
06364 1	4	142	29	10
06365 8	5	163	33	10
06366 5	6	184	38	10
06367 2	7	194	41	5
06368 9	8	206	44	10
06369 6	10	231	50	5
06370 2	12	259	57	5
06371 9	14	291	70	5

For Allen screws (metric).



352 H9B Hex L-key set in holder.

Manganese-phosphated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	Blade	Length	Width	Height
06386 3	352 H9B			5
352B	1.5 2 2.5 3 4 5 6 8 10			




NEW

352 H7B Hex L-key set in holder.

Manganese-phosphated, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	Blade	Length	Width	Height
06384 9	352 H7B			5
352B	1.5 2 2.5 3 4 5 6			



352 HM5B Hex L-key set in holder.

Manganese-phosphated, 5 pcs.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ISO 2936L.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	Blade	Length	Width	Height
06382 5	352 HM5B			10
352B	0.7 0.9 1.3 1.5 2			

Wiha Info

Colour-coding system:

- red:
metric hex blades
- yellow:
inch hex blades
- green:
TORX® blades
- light green:
TORX PLUS® blades

Wiha hex L-keys (metric).

For Allen screws (metric).



351 Hex L-key, short.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.

Order-No.	⊙	↔	⊥	⊥
01144 4	1.5	46	15	10
01145 1	2	51	18	10
01146 8	2.5	57	20	10
01147 5	3	64	23	10
01148 2	3.5	70	26	5
01149 9	4	72	29	10
01150 5	4.5	80	31	5
01151 2	5	83	33	10
01152 9	5.5	90	35	5
01153 6	6	94	38	10
01154 3	7	99	41	5
01155 0	8	105	44	10
01156 7	9	114	47	5
01157 4	10	119	50	5
01158 1	11	129	53	5
01159 8	12	134	57	5
01160 4	14	151	70	5
01161 1	17	173	80	5
01162 8	19	195	89	5



351 H9 Hex L-key set in holder. Nickel-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.
Extra: Thanks to its compact dimensions, this holder fits easily into every ruler pocket.
Popular key sizes kept in a well-organised holder.

Order-No.	⊙	↔	⊥	⊥
01174 1	351 H9			10
⊙	351	1.5 2 2.5 3 4 5 6 8 10		

SB 351 H9 Hex L-key set in holder. Nickel-plated, 9 pcs. Blister packed.

Order-No.	⊙	↔	⊥	⊥
03734 5	SB 351 H9			5
⊙	351	1.5 2 2.5 3 4 5 6 8 10		

For Allen screws (metric).



351 H7 Hex L-key set in holder. Nickel-plated, 7 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	⊙	↔	⊥	⊥
01172 7	351 H7			10
⊙	351	1.5 2 2.5 3 4 5 6		



351 B8 Hex L-key set in sliding box. Nickel-plated, 8 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.
Extra: Small, impact resistant sliding box.

Order-No.	⊙	↔	⊥	⊥
01166 6	351 B8			10
⊙	351	2 2.5 3 4 5 6 8 10		



351 R8 Hex L-key set on keyring. Nickel-plated, 8 pcs. In plastic pouch.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.
Extra: Flexible hanging of all keys on a keyring.

Order-No.	⊙	↔	⊥	⊥
01180 2	351 R8			10
⊙	351	2 2.5 3 4 5 6 8 10		

For Allen screws (metric).



351 VB Hex L-key set in bench stand. Nickel-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: ISO 2936K.
Extra: Robust metal workbench holder to place on workbench or wall-mount.
Tip diagrams printed to scale.

Order-No.	⊙	↔	⊥	⊥
01182 6	351 VB			1
⊙	351	2.5 3 4 5 6 8 10 12 14		



359 Hex L-key with pivot.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: DIN 6911.
Application: Fits hex socket screws with low head and centre hole.
With key guidance according to DIN 6912.

Order-No.	⊙	↔	⊥	⊥
01255 7	3	64	23	10
01256 4	4	72	29	10
01257 1	5	83	33	10
01258 8	6	94	38	10
01259 5	8	105	44	10
01260 1	10	119	50	5
01261 8	12	134	57	5
01262 5	14	151	70	5
01263 2	17	173	80	5

For Allen screws (metric).



350 Hex L-key, short.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: ISO 2936K.

Order-No.	⊙	↔	⊥	⊥
06218 7	1.3	41	13	10
01121 5	1.5	46	15	10
01122 2	2	51	18	10
01123 9	2.5	57	20	10
01124 6	3	64	23	10
01126 0	4	72	29	10
01128 4	5	83	33	10
01130 7	6	94	38	10
01131 4	7	99	41	10
01132 1	8	105	44	10
01133 8	9	112	47	5
01134 5	10	119	50	5
01135 2	11	126	53	5
01136 9	12	134	57	5
01137 6	14	151	70	5
01138 3	17	173	80	5
01139 0	19	195	89	5
01140 6	22	217	102	1
01141 3	24	241	114	1
01142 0	27	271	127	1
01143 7	32	339	157	1



350 H9 Hex L-key set in holder. Manganese-phosphated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: ISO 2936K.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	⊙	↔	⊥	⊥
06379 5	350 H9			10
⊙	350	1.5 2 2.5 3 4 5 6 8 10		



NEW 350 H7 Hex L-key set in holder. Manganese-phosphated, 7 pcs.

Order-No.	⊙	↔	⊥	⊥
06378 8	350 H7			10
⊙	350	1.5 2 2.5 3 4 5 6		

Wiha hex L-keys (inch).

For Allen screws (inch).



369 Zoll Ball end hex L-key, long. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ASME B18.3.
Application: Especially for inch-sized screws that are difficult to access.
Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	●	↔	└	mm	▬
01422 3	0.05	72	13	1.27	10
01423 0	1/16	80	15	1.59	10
01431 5	5/64	88	18	1.98	10
01427 8	3/32	101	20	2.38	10
01433 9	7/64	111	21	2.78	10
01425 4	1/8	121	23	3.18	10
01434 6	9/64	136	27	3.57	10
01430 8	5/32	148	29	3.97	10
01426 1	3/16	163	33	4.76	10
01432 2	7/32	176	36	5.56	10
01424 7	1/4	191	38	6.35	10
01429 2	5/16	210	43	7.94	10
01428 5	3/8	232	50	9.53	5

For Allen screws (inch).



369 SZ13B Ball end hex L-key set in ProStar. Manganese-phosphated, 13 pcs. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ASME B18.3.
Application: Especially for inch-sized screws that are difficult to access.
Extra: Space saving ProStar allows the easy removal of each key without moving any others.

Order-No.	▬	
24189 6	369 SZ13B	5
●	369 Zoll	0.05 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8

SB 369 SZ13B Ball end hex L-key set in ProStar. Manganese-phosphated, 13 pcs. Inch sizes. Blister packed.

Order-No.	▬	
24851 2	SB 369 SZ13B	5
●	369 Zoll	0.05 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8



369 HZ8 Ball end hex L-key set in holder. Manganese-phosphated, 8 pcs. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, manganese-phosphated.
Standards: Based on ASME B18.3.
Application: Especially for inch-sized screws that are difficult to access.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	▬	
01420 9	369 HZ8	5
●	369 Zoll	5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16

SB 369 HZ8 Ball end hex L-key set in holder. Manganese-phosphated, 8 pcs. Inch sizes. Blister packed.

Order-No.	▬	
02939 5	SB 369 HZ8	5
●	369 Zoll	5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16

For Allen screws (inch).



351 Zoll Hex L-key, short. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ASME B18.3.
Application: For all popular inch screws.

Order-No.	●	↔	└	mm	▬
25626 5	0.05	41	13	1.27	10
01184 0	1/16	47	16	1.59	10
01194 9	5/64	51	18	1.98	10
01189 5	3/32	55	22	2.38	10
22406 6	7/64	58	21	2.78	10
01187 1	1/8	61	23	3.18	10
01200 7	9/64	65	25	3.57	10
01193 2	5/32	72	29	3.97	10
01188 8	3/16	76	30	4.76	10
01197 0	7/32	84	34	5.56	10
01186 4	1/4	94	37	6.35	10
01192 5	5/16	106	43	7.94	10
01191 8	3/8	117	48	9.53	5
01185 7	1/2	143	59	12.70	5
01198 7	9/16	158	64	14.29	5
01195 6	5/8	176	71	15.88	5
01190 1	3/4	198	89	19.05	5



351 SZ13 Hex L-key set in ProStar. Nickel-plated, 13 pcs. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ASME B18.3.
Application: For all popular inch screws.
Extra: Space saving ProStar allows the easy removal of each key without moving any others.

Order-No.	▬	
25610 4	351 SZ13	5
●	351 Zoll	41 1/16 5/64 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 5/16 3/8



351 HZ8 Hex L-key set in holder. Nickel-plated, 8 pcs. Inch sizes.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Standards: Based on ASME B18.3.
Application: For all popular inch screws.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.

Order-No.	▬	
01176 5	351 HZ8	10
●	351 Zoll	5/64 3/32 1/8 5/32 3/16 7/32 1/4 5/16

For Allen screws (metric).



NEW 369F Ball end hex L-key, long.

Blade: Chrome vanadium steel, through-hardened, colour-coded.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: The ball end enables the user to work at angles up to 25°. Colour coding for immediate identification of L-keys.

Order-No.	●	↔	└	mm	▬
34269 2	1.5	91	15	black	10
34270 8	2	101	18	green	10
34271 5	2.5	113	20	turquoise	10
34272 2	3	128	23	light blue	10
34273 9	4	142	29	purple	10
34274 6	5	163	33	red	10
34275 3	6	184	38	orange	10
34276 0	8	206	44	yellow	10
34277 7	10	231	50	grey	5



NEW 369 H9F Ball end hex L-key set in holder.

Blade: Chrome vanadium steel, through-hardened, colour-coded.
Standards: Based on ISO 2936L.
Application: Especially for screws that are difficult to access.
Extra: Popular key sizes kept in a well-organised holder.
Simple, rapid operation with solid stopping point for L-keys.
The ball end enables the user to work at angles up to 25°. Colour coding for immediate identification of L-keys.

Order-No.	▬	
34268 5	369 H9F	5
●	369F	1.5 2 2.5 3 4 5 6 8 10