



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Insulation Boots & Sleeves



Insulation Boot & Sleeve Product Type: **Insulation Boot**

Primary Product Material: **PVC**

Primary Product Color: **Blue**

Packaging Method: **Bag**

Features

Product Type Features

Insulation Boot & Sleeve Product Type	Insulation Boot
---------------------------------------	-----------------

Body Features

Primary Product Material	PVC
Primary Product Color	Blue

Dimensions

Product Length	59 mm[2.323 in]
----------------	-----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2020 (205)



SVHC > Threshold:
DEHP (20.75% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-925552-0
AM WIRE PIN 20-17 AWG .0126 PTPPB



TE Part #2312042-5
EP II HSG, 5POS.,GLOW WIRE



TE Part #3-2299280-2
POD-LOK 250 FLAG AWG 16-14
PTPBR GF



TE Part #2299287-2
POD-LOK 187 FLAG AWG 20-16
PTPBR GF



TE Part #160739-4
250 FASTON,PIGGYBACK REC.,18-14
AWG,TPPB



TE Part #2324579-8
HOUSING, PLUG, 8P, DUAL ROW,
EP2.5



TE Part #1-2324201-4
HSG,REC,FREE-HANGING,GWT,
DUALROW,EP2.5



TE Part #2324582-8
HSG,REC,FREE HANGING,DUALROW,
EP2.5



Documents

CAD Files

Customer View Model

ENG_CVM_1766600-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1766600-4_B.3d_stp.zip

English

Customer View Model

ENG_CVM_1766600-4_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

Busbar Power Brochure

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English