




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Multiple Contact Types	Without
Contact Layout	Matrix
Contact Type	Socket
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	4.2 mm[.165 in]

Dimensions

Row-to-Row Spacing	4.2 mm[.165 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 770904-1
MINI UMNLSOK 22-18 AWG SN



TE Part # 170366-3
MINI UNIVERSAL M-N-L SOCKET LP




TE Part # 170366-4
MINI UNIVERSAL M-N-L SOCKET LP



TE Part # 171639-1
MINI U-M-N-L SOCKET L.P




TE Part # 794407-1
MINI UNML SCKT 20-16 AWG SN




TE Part # 770987-1
MINI UMNL PIN 22-18AWG SN LP



TE Part # 1-770834-0
MINI UMNL SOK AU LF



TE Part # 1-770903-1
MINI UMNL PIN 22-18 AWG AU LP



TE Part # 1-770988-0
MINI UMNL SOK 22-18AWG AU




TE Part # 1-794407-0
MINI UMNL SOK 20-16 AWG AU LF




TE Part # 170361-4
UNIV. M-N-L SOC.



TE Part # 170364-1
MINI UNIVERSAL M-N-L PIN LP



TE Part # 170359-3
MINI UNIVERSAL M-N-L PIN



TE Part # 170361-3
MINI UNIVERSAL M-N-L SOCKET




TE Part # 770835-1
MINI UMNL PIN SN



TE Part # 770901-1
MINI UMNL PIN 26-22 AWG SN




TE Part # 770904-6
MINI UMNL SOK CONT 22-18AWG AU



TE Part # 770903-1
MINI UMNL PIN 22-18 AWG SN



TE Part # 770986-1
MINI UMNL SOK 26-22AWG SN LP



TE Part # 770987-3
MINI UMNL PIN 22-18 AWG AU LP

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(89)



Connector Hardware(4)




Connector Seals & Cavity Plugs(17)



Connector Strain Relief(2)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(93)




Rectangular Power Connectors(196)




Wire-to-Board Headers & Receptacles (93)

Customers Also Bought



TE Part #1586314-1
VAL-U-LOK PIN BR TN 22-18 LP




TE Part #5069824023
CGPT-3.2/1.6-0-SP



TE Part #0413-003-1605
SEALING PLUG, SIZE 16, BLU



TE Part #925075
4W CIRCULAR MATE-N-LOK PIN HSG NAT



TE Part #1586000-4
4P FH PLUG VAL-U-LOK V2




TE Part #CAT-J41-DDRC
DEUTSCH DT Receptacle Connectors



TE Part #W6P
WEDGE LOCK, 6P, REC, GRN, DT



TE Part #2294417-1
INDUSTRIAL MINI I/O HDR TYPE I EMBOSS



TE Part #1-1721538-3
OJ-SH-112HM2,000

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-172171-9_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-172171-9_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-172171-9_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English