

SpeedClic Accessory Set (SC690)



Features & Benefits

Features & Benefits

- Assortment of 10 SpeedClic cutting wheels and the special SpeedClic mandrel. Besides 6 regular 38 mm metal cutting wheels the kit includes 2 special thin cutting wheels and 2 unique plastic cutting wheels.

Order number: 2615S690JA

EAN-Code: 8710364045839

DREMEL® SpeedClic®: Plastic Cutting Wheels 5-Pack. (SC476)

The cutting wheels are specially designed for cutting in all sorts of plastics. Quick, Easy, Keyless.

3,2 mm



Features & Benefits

Contents

- The cutting wheels are specially designed for cutting in all sorts of plastics. Quick, Easy, Keyless.

Technical specification

Shank diameter: 3,2 mm

Working diameter: 38,0 mm

Maximum RPM: 35.000 1/min

Quantity: 5

Order number: 2615S476JB

DREMEL® SpeedClic®: Metal Cutting Wheels 5-Pack. (SC456)

Dremel, the inventor of the SpeedClic quick-change system for rotary tool accessories, now offers an extended line of SpeedClic metal cutting accessories. The Starter Set SC406 includes the unique SpeedClic mandrel and two fiberglass reinforced metal cutting wheels. The SC456, SC456B and SC409 are replacement metal cutting wheels, whereby the SC409 wheels have a thickness of just 0,75 mm.

3,2 mm



Features & Benefits

Contents

- The fiberglass reinforced cutting wheels are for cutting in all sorts of metals. Quick, Easy, Keyless.

Technical specification

Shank diameter: 3,2 mm

Working diameter: 38,0 mm

Maximum RPM: 35.000 1/min

Quantity: 5

Order number: 2615S456JC

DREMEL® SpeedClic®: Thin Cutting Wheels 5-Pack. (SC409)

Dremel, the inventor of the SpeedClic quick-change system for rotary tool accessories, now offers an extended line of SpeedClic metal cutting accessories. The Starter Set SC406 includes the unique SpeedClic mandrel and two fiberglass reinforced metal cutting wheels. The SC456, SC456B and SC409 are replacement metal cutting wheels, whereby the SC409 wheels have a thickness of just 0,75 mm.

3,2 mm



Features & Benefits

Contents

- The fiberglass reinforced cutting wheels are just 0,75 mm thick. They are perfect for precise cutting in all sorts of metals. Quick, Easy, Keyless.

Technical specification

Shank diameter: 3,2 mm

Working diameter: 38,0 mm

Maximum RPM: 35.000 1/min

Quantity: 5

SpeedClic Mandrel (SC402)

Mandrels are used to mount different accessories, like felt polishing wheels or cut-off wheels.

3,2 mm



Features & Benefits

Features & Benefits

- Mandrel for the SpeedClic accessories. Quick, Easy, Keyless.

Technical specification

Shank diameter: 3,2 mm

Maximum RPM: 35.000 1/min

Quantity: 1

Order number: 2615S402JB

EAN-Code: 8710364042838