

## Protective covers - HC-STA-D07-HCLWS-PLR-BK - 1419274


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective cover D7, with single locking latch, material: PA, protective cover material: PA, height: 30 mm, seal: yes, Standard, With lanyard, diameter of retaining cord eyelet: 25 mm, for socket inserts



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 160252
GTIN	4055626160252
Weight per Piece (excluding packing)	13.600 g
Custom tariff number	85389099
Country of origin	China

### Technical data

#### Dimensions

Height	30 mm
Width	24.2 mm
Length	24.2 mm

#### Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	D7
Type	For sleeve housing without single locking latch
Housing type	Protective cover
Color	black
Locking type	with single locking latch
Material	PA
Housing material	PA

## Protective covers - HC-STA-D07-HCLWS-PLR-BK - 1419274

### Technical data

#### General


Seal material	NBR
Material lock	PA
Material, protective cover	PA
Flammability rating according to UL 94	V0 (Polyamide housing)
Connection	Plastic protective cover for short-term protection

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

Dimensional drawing



Dimensional drawing

### Classifications

#### eCl@ss

eCl@ss 5.1	27269200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

#### ETIM

ETIM 5.0	EC002314
----------	----------

## Protective covers - HC-STA-D07-HCLWS-PLR-BK - 1419274

### Classifications

#### ETIM

ETIM 6.0	EC002314
ETIM 7.0	EC002314

#### UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

### Approvals


#### Approvals

#### Approvals

EAC / DNV GL

#### Ex Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01102
-----	-------------------------------------------------------------------------------------	--------------------------

DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAE000037S
--------	-------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------	------------

### Accessories

#### Accessories

#### Housing latches

Housing brackets - HC-D07-SL-PLBK - 1424440



Replacement latch for HC-D7 housing

