
Conductive Sensors Level Probes Types VT, VTI





- Excellent resistance to chemicals
- Teflon housing
- 1 to 4 electrodes
- Isolated (teflon) or unisolated electrodes
- Cable connection
- 1 1/2" pipe thread according to ISO 228/1-Gx"

Product Description

Level sensor for measuring the level of conductive liquids, i.e. max./min. control of charging for discharging. The function is determined by the amplifier relay used. The sensors are delivered with standard length electrodes these are cut off to suit the application. The teflon housing makes the sensor excellent for use in rough environments.

Ordering Key

VTI 4

Type — Housing material — Isolated — Number of electrodes


Type Selection

Pipe thread	Electrode isolation	Ordering no. 1 electrode	Ordering no. 2 electrodes	Ordering no. 3 electrodes	Ordering no. 4 electrodes
1 1/2"	No	VT 1	VT 2	VT 3	VT 4
1 1/2"	Yes	VTI 1	VTI 2	VTI 3	VTI 4

Specifications

Electrodes Isolation			
VTI	Teflon (PTFE)		
Material	Stainless steel		
Standard length	100 cm		
Diameter	Ø 5 mm		
Housing			
Material	Teflon (PTFE)		
Connection	Cable (silicone), 100 cm		
Environment			
Degree of protection	IP 67		
Operating temperature	0 to +145°C (+32° to +275°F)		
Storage temperature	-40° to +160°C (-40° to +320°F)		
Pressure	4 bar at 143°C		

Dimensions



Mode of Operation

The length of the electrodes determines the levels which will be detected and the amplifier chosen determines the function (see SV..., S195/196, S1961, ELA, ELC

or ELD). If the container is made of a conductive material this can be used as common electrode.

Accessories

Extension joint for Ø5 mm electrodes:

VD1