Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

SECTION 1: Identification of the substance/mixture and of the company/undertaking

· **1.1 Product identifier**

· **Trade name: PressurePro Solar Cleaner RM 99**

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
· **Application of the substance / the mixture** High pressure cleaner

· **1.3 Details of the supplier of the safety data sheet**
· **Manufacturer/Supplier:**

Alfred Kärcher SE & Co. KG
Alfred-Kärcher-Str. 28-40
D - 71364 Winnenden
Tel.: +49-7195-14-0

Kärcher (UK) Ltd.
Kärcher House
Brookhill Way
Banbury
Oxon OX16 3ED
Great Britain
Tel.: +44-1295-752-000

Internet: www.karcher.com

· **Further information obtainable from:**

Regulatory Affairs
Tel.: +49-7195-14-0
productsafety.management.de@karcher.com

· **1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incidents
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
Outside USA and Canada: +1-703-527-3887 (collect calls accepted)

SECTION 2: Hazards identification

· **2.1 Classification of the substance or mixture**
· **Classification according to Regulation (EC) No 1272/2008**

Eye Irrit. 2	H319 Causes serious eye irritation.
Aquatic Chronic 3	H412 Harmful to aquatic life with long lasting effects.

· **2.2 Label elements**
· **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.

(Contd. on page 2)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 1)

· **Hazard pictograms**



GHS07

· **Signal word** Warning
· **Hazard statements**
H319 Causes serious eye irritation.
H412 Harmful to aquatic life with long lasting effects.
· **Precautionary statements**

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P264	Wash hands thoroughly after handling.
P273	Avoid release to the environment.
P280	Wear eye protection / face protection.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313	If eye irritation persists: Get medical advice/attention.
P501	Dispose of contents/container in accordance with local/regional/national/international regulations.

SECTION 3: Composition/information on ingredients

· **3.2 Mixtures**
· **Description:** Cleaning agent

· **Dangerous components:**

CAS: 112-34-5 EINECS: 203-961-6 Index number: 603-096-00-8 Reg.nr.: 01-2119475104-44-xxxx	2-(2-butoxyethoxy)ethanol Eye Irrit. 2, H319	1-5%
CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25-xxxx	propan-2-ol Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	1-5%
CAS: 68439-51-0	Fatty alcohol ethoxylate Acute Tox. 4, H302; Eye Irrit. 2, H319; Aquatic Chronic 3, H412	≥2.5-<5%
	Polyamine, anionically modified Eye Dam. 1, H318; Acute Tox. 4, H332	≥1-<3%
CAS: 95-14-7 EINECS: 202-394-1 Index number: 613-350-00-X Reg.nr.: 01-2119979079-20-xxxx	benzotriazole Aquatic Chronic 2, H411; Acute Tox. 4, H302	≥1-<2.5%
CAS: 2605-79-0 EINECS: 220-020-5 Reg.nr.: 01-2119959297-22	decyldimethyl aminoxide Eye Dam. 1, H318; Aquatic Acute 1, H400; Aquatic Chronic 2, H411; Acute Tox. 4, H302	≥1-<2.5%

(Contd. on page 3)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 2)

· **Additional information** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**
· **After inhalation** Supply fresh air; consult doctor in case of complaints.
· **After skin contact** Generally the product does not irritate the skin.
· **After eye contact** Rinse opened eye for several minutes under running water.
· **After swallowing**
Rinse out mouth and then drink plenty of water.
If symptoms persist consult doctor.

· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**
· **Suitable extinguishing agents**
CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

· **5.2 Special hazards arising from the substance or mixture** No further relevant information available.

· **5.3 Advice for firefighters**
· **Protective equipment:** No special measures required.
· **Additional information** Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures** Not required

· **6.2 Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
Do not allow to penetrate the ground/soil.

· **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).
Ensure adequate ventilation.

· **6.4 Reference to other sections**
See Section 7 for information on safe handling
See Section 8 for information on personal protection equipment.

(Contd. on page 4)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 3)

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
Avoid contact with eyes and skin.
· **Information about fire - and explosion protection:** No special measures required.

· **7.2 Conditions for safe storage, including any incompatibilities**
· **Storage**
· **Requirements to be met by storerooms and receptacles:** No special requirements.
· **Information about storage in one common storage facility:** Keep away from food, beverages and feed.
· **Further information about storage conditions:** Keep receptacle tightly sealed.

· **7.3 Specific end use(s)** No further relevant information available.

*
SECTION 8: Exposure controls/personal protection

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**	
112-34-5 2-(2-butoxyethoxy)ethanol	
WEL	Short-term value: 101.2 mg/m³, 15 ppm Long-term value: 67.5 mg/m³, 10 ppm
67-63-0 propan-2-ol	
WEL	Short-term value: 1250 mg/m³, 500 ppm Long-term value: 999 mg/m³, 400 ppm

· **DNELs**		
67-63-0 propan-2-ol		
Oral	DNEL	26 mg/kg×d (consumer)
Dermal	DNEL	888 mg/kg×d (employee)
		319 mg/kg×d (consumer)
Inhalative	DNEL	500 mg/m3 (employee)
		89 mg/m3 (consumer)

· **PNECs**	
67-63-0 propan-2-ol	
PNEC	140.9 mg/l (freshwater)
	140.9 mg/l (marine water)
	140.9 mg/l (STP)
	2251 mg/l (STP)
PNEC sediment	552 mg/kg (freshwater)

(Contd. on page 5)

(Contd. of page 4)

PNEC soil	552 mg/kg (marine water) 28 mg/kg (soil)

· **8.2 Exposure controls**
· **Appropriate engineering controls** No further data; see section 7.
· **Individual protection measures, such as personal protective equipment**
· **General protective and hygienic measures**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Avoid contact with the eyes and skin.
· **Respiratory protection:** Not necessary if room is well-ventilated.
· **Hand protection**



Protective gloves.

· **Material of gloves** Butyl rubber, BR
· **Penetration time of glove material**
The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.
· **Eye/face protection**



Tightly sealed goggles (EN 166)

*

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**
· **General Information**

· **Physical state**	Liquid
· **Colour:**	Colourless
· **Odour:**	Alcohol-like
· **Odour threshold:**	Not determined
· **Melting point/freezing point:**	-1 °C
· **Boiling point or initial boiling point and boiling range**	100 °C
· **Flammability**	Not applicable
· **Lower and upper explosion limit**	
· **Lower:**	Not determined
· **Upper:**	Not determined
· **Flash point:**	62 °C (Closed Cup)
· **Auto-ignition temperature:**	not applicable
· **Decomposition temperature:**	Not determined
· **pH at 20 °C**	9
· **pH-value 1 %:**	7-9

(Contd. on page 6)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 5)

· **Viscosity:**	
· **Kinematic viscosity**	Not determined
· **dynamic:**	Not determined
· **Solubility**	
· **Water:**	Fully miscible
· **Partition coefficient n-octanol/water (log value)**	Not determined
· **Vapour pressure:**	Not determined
· **Density and/or relative density**	
· **Density at 20 °C:**	1.006 g/cm³
· **Relative density**	Not determined
· **Vapour density**	Not determined
· **Relative gas density**	Not determined
· **Particle characteristics**	Not applicable

· **9.2 Other information**

· **Appearance:**

· **Form:**	Fluid

· **Important information on protection of health and environment, and on safety.**

· **Ignition temperature:**	Product is not selfigniting.
· **Explosive properties:**	Not determined

· **Change in condition**

· **Evaporation rate**	Not determined

· **Information with regard to physical hazard classes**

· **Explosives**	Void
· **Flammable gases**	Void
· **Aerosols**	Void
· **Oxidising gases**	Void
· **Gases under pressure**	Void
· **Flammable liquids**	Void
· **Flammable solids**	Void
· **Self-reactive substances and mixtures**	Void
· **Pyrophoric liquids**	Void
· **Pyrophoric solids**	Void
· **Self-heating substances and mixtures**	Void
· **Substances and mixtures, which emit flammable gases in contact with water**	Void
· **Oxidising liquids**	Void
· **Oxidising solids**	Void
· **Organic peroxides**	Void
· **Corrosive to metals**	Void
· **Desensitised explosives**	Void

SECTION 10: Stability and reactivity

· **10.1 Reactivity** corresponds to 10.3

(Contd. on page 7)

(Contd. of page 6)

· **10.2 Chemical stability**
· **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

· **10.3 Possibility of hazardous reactions** No dangerous reactions known

· **10.4 Conditions to avoid** No further relevant information available.

· **10.5 Incompatible materials:** No further relevant information available.

· **10.6 Hazardous decomposition products:** No dangerous decomposition products known

SECTION 11: Toxicological information

· **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
· **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**		
112-34-5 2-(2-butoxyethoxy)ethanol		
Oral	LD50	2410 mg/kg (mouse) (OECD 401)
Dermal	LD50	2764 mg/kg (Rabbit)
67-63-0 propan-2-ol		
Oral	LD50	5840 mg/kg (Rat) (OECD 401)
Dermal	LD50	13900 mg/kg (Rabbit) (OECD 402)
95-14-7 benzotriazole		
Oral	LD50	500 mg/kg (Rat)
2605-79-0 decyldimethyl aminoxide		
Oral	LD50	301-2000 mg/kg (Rat)

· **Primary irritant effect:**
· **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
· **Serious eye damage/irritation** Causes serious eye irritation.
· **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
· **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
· **Carcinogenicity** Based on available data, the classification criteria are not met.
· **Reproductive toxicity** Based on available data, the classification criteria are not met.
· **STOT-single exposure** Based on available data, the classification criteria are not met.
· **STOT-repeated exposure** Based on available data, the classification criteria are not met.
· **Aspiration hazard** Based on available data, the classification criteria are not met.
· **11.2 Information on other hazards**

· **Endocrine disrupting properties**		
95-14-7	benzotriazole	List II

(Contd. on page 8)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 7)

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**	
112-34-5 2-(2-butoxyethoxy)ethanol	
LC50/96 h	1300 mg/l (Lepomis macrochirus)
EC10/16 h	1170 mg/l (Pseudomonas putida)
EC50/24 h	2850 mg/l (Daphnia magna) (DIN 38412)
NOEC	>100 mg/l (Desmodesmus subspicatus)
67-63-0 propan-2-ol	
LC50/96 h	9640 mg/l (Pimephales promelas)
EC50/48 h	13299 mg/l (Daphnia magna)
EC50/72 h	>1000 mg/l (Desmodesmus subspicatus)
EC10/18 h	>1000 mg/l (Pseudomonas putida) (DIN 38412)
95-14-7 benzotriazole	
LC50/96 h	180 mg/l (Danio rerio) (OECD 203)
EC50/48 h	15.8 mg/l (Aquatic invertebrates) (OECD 202)
EC50	1060 mg/l /3 h (STP) (OECD 209)
ErC10/72h	1.18 mg/l (Pseudokirchneriella subcapitata)
2605-79-0 decyldimethyl aminoxide	
LC50/96 h	31.8 mg/l (Brachydanio rerio) (OECD 203)
EC50/48 h	3.43 mg/l (Daphnia magna) (OECD 202)
EC50/72 h	0.16 mg/l (Pseudokirchneriella subcapitata) (OECD 201)

· **12.2 Persistence and degradability** No further relevant information available.

· **Degree of elimination:**	
112-34-5 2-(2-butoxyethoxy)ethanol	
OECD 301C	80-90 % (28 d)
OECD 301E	>70 % (28 d)
OECD 302B	100 % (28 d)

· **12.3 Bioaccumulative potential** No further relevant information available.

· **12.4 Mobility in soil** No further relevant information available.

· **12.5 Results of PBT and vPvB assessment**
· **PBT:** Not applicable
· **vPvB:** Not applicable
· **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.

(Contd. on page 9)

(Contd. of page 8)

· **12.7 Other adverse effects**
· **Additional ecological information:**

· **General notes:**

Do not allow product to reach ground water, water course or sewage system.

Danger to drinking water if even small quantities leak into the ground.

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

The product does not contain organically bounded halogens (AOX-free).

The contained organic complexing agents reach a DOC-elimination grade of 80% (corresponding to No. 406 of Annex "Analytic and measuring methods") and with this meet the tightened demands of Annex 49 of the revised Direction on liqid waste.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**
· **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Must be specially treated adhering to official regulations.

· **European waste catalogue**	
20 01 29*	detergents containing hazardous substances

· **Uncleaned packaging:**
· **Recommendation:**
Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.
· **Recommended cleansing agents:** Water, if necessary together with cleaning agents.

SECTION 14: Transport information

· **14.1 UN number or ID number**	
· **ADR, IMDG, IATA**	Void
· **14.2 UN proper shipping name**	
· **ADR, IMDG, IATA**	Void
· **14.3 Transport hazard class(es)**	
· **ADR, ADN, IMDG, IATA**	
· **Class**	Void

(Contd. on page 10)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 9)

· **14.4 Packing group** · **ADR, IMDG, IATA**	Void
· **14.5 Environmental hazards:**	Not applicable
· **14.6 Special precautions for user**	Not applicable
· **14.7 Maritime transport in bulk according to IMO instruments**	Not applicable
· **UN "Model Regulation":**	Void

SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
· **Poisons Act**

· **Regulated explosives precursors**
None of the ingredients is listed.

· **Regulated poisons**
None of the ingredients is listed.

· **Reportable explosives precursors**
None of the ingredients is listed.

· **Reportable poisons**

1310-73-2	sodium hydroxide	12% of total caustic alkalinity

· **Directive 2012/18/EU**
· **Named dangerous substances - ANNEX I** None of the ingredients is listed.

· **National regulations**

· **Information about limitation of use:** Employment restrictions concerning juveniles must be observed.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.
A product information sheet can be provided if requested.

· **Relevant phrases**
H225 Highly flammable liquid and vapour.
H302 Harmful if swallowed.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H332 Harmful if inhaled.
H336 May cause drowsiness or dizziness.

(Contd. on page 11)

Safety data sheet
according to UK REACH

Printing date 30.01.2026 Version number 12 (replaces version 11) Revision: 20.08.2024

Trade name: PressurePro Solar Cleaner RM 99

(Contd. of page 10)

H400 Very toxic to aquatic life.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.

· **Contact:**
Regulatory Affairs
Tel.: +49-7195-14-0
productsafety.management.de@karcher.com

· **Abbreviations and acronyms:**
ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
DNEL: Derived No-Effect Level (UK REACH)
PNEC: Predicted No-Effect Concentration (UK REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Flam. Liq. 2: Flammable liquids – Category 2
Acute Tox. 4: Acute toxicity – Category 4
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1
Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2
Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· *** Data compared to the previous version altered.**

· 0·011-339·0 RM 99/4 2·736