



**FAG****6324-C4**

Deep groove ball bearing

Deep groove ball bearing 63, single row, steel
sheet metal cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	120 mm	Bore diameter
D	260 mm	Outside diameter
B	55 mm	Width
C_r	225,000 N	Basic dynamic load rating, radial
C_{0r}	195,000 N	Basic static load rating, radial
C_{ur}	9,800 N	Fatigue load limit, radial
n_G	3,500 1/min	Limiting speed
n_{gr}	3,800 1/min	Reference speed
$\approx m$	12.7 kg	Weight



Mounting dimensions

$d_{a\min}$	134 mm	Minimum diameter shaft shoulder
$D_{a\max}$	246 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	215.6 mm	Shoulder diameter outer ring
d_1	165.8 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

f_0	13.8	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed