## **PUSHBUTTON SWITCHES**

#### **Low Cost Sealed**

The Series 47 is a uniquely designed miniature pushbutton switch with a epoxy sealed base. Meet respective IP67 requirements. The buttons are available in seven different colors. All this at a very affordable price.

#### **APPLICATIONS**

- Marine equipment
- · Medical equipment
- · Outdoor controls
- · Food processing equipment
- Recreational vehicles



ACTUAL SIZE

#### **KEY FEATURES:**

- Sealed to IP67
- Small size
- 7 button colors

- · Long life
- · Low cost

#### **ORDERING INFORMATION:**

Part Number	Button Color	Epoxy Sealed Base	
47-1111	Black	✓	
47-1121	Red	✓	
47-1131	Green	✓	
47-1141	White	✓	
47-1151	Yellow	✓	
47-1161	Blue	✓	
47-1171	Orange	✓	

### STANDARDS / AGENCY / RATINGS:












# SCHEMATIC FORM A SPST-NO



Installation of a bi-directional TVS diode between the outer terminal of the switch and ground is recommended to avoid voltage spikes. Consult the factory for details.



Travel (nom):

.020 inches

Life:

100,000 cycles

**Operating force:** 

1,000 grams (nominal)

Sealed to:

**IP67** 

**Operating temperature:** 

-40°C to +85°C

**Button material:** 

silicone

Contact:

metal snap dome providing

a tactile feel

Terminal finish:

gold over nickel

**Dielectric strength:** 

1,000 VAC

**Insulation resistance:** 

 $10.000~\mathrm{M}\Omega$ 

**Contact resistance (initial):** 

<100  $\Omega$ 

**Current rating:** 

20 mA @ 28 VDC

**Switch terminals** 

mate with:

Pancon Mas-Con

Connector CE100F24-3-DB

Recommended panel

cutout:

0.565" / 0.560" diameter

(ø14.40 / 14.22)

**Recommended panel** 

thickness:

0.060" (1.52) max