



## Main

Range of product	Canalis
Product name	KS
Product or component type	Adapter
Product compatibility	KS
[Ie] rated operational current	400 A 500 A

## Complementary

Accessory / separate part category	Adaptation
Mounting location	Between trunking
Mounting mode	By screws
Mounting support	Busbar
Busbar trunking polarity	3L + N + PE
Width	324 mm
Depth	142 mm
Height	200 mm

## Environment

IP degree of protection	IP55 conforming to IEC 60529
Standards	IEC 60439-2 IEC 61439-6

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins