




PRODUCT-DETAILS

OT1600E04K

OT1600E04K SWITCH-DISCONNECTOR



General Information	
Extended Product Type	OT1600E04K
Product ID	1SCA108358R1001
EAN	6417019416755
Catalog Description	OT1600E04K SWITCH-DISCONNECTOR
Long Description	4-pole, front operated, base mounted switch-diconnector with black direct mount handle, terminal bolt kit included

ABB EcoSolutions	
End Of Life Disassembling Instructions	1SCC301120M0201
Environmental Information	1SCC301233D0201
Environmental Product Declaration - EPD	1SCC301300D0201

Material Compliance		
Conflict Minerals Reporting Template (CMRT)		9AKK108467A5658
REACH Declaration		1SCC011021D0201
RoHS Declaration		1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019	
Toxic Substances Control Act - TSCA		1SCC011025D0201

Popular Downloads		
Data Sheet, Technical Information		1SCC301020C0201
Instructions and Manuals		1SCC301047M0213
Mechanical Drawings		1SCC301727F0002 1SCC301726F0002
Environmental Product Declaration - EPD		1SCC301300D0201

Environmental		
Degree of Protection		Front IP00
Environmental Information		1SCC301233D0201
Pollution Degree		3

Ordering		
Minimum Order Quantity		1 piece
Customs Tariff Number		85365080
Country or Territory of Origin		Finland

Dimensions		
Product Net Width		414.5 mm
Product Net Height		372 mm
Product Net Depth / Length		237.5 mm
Product Net Weight		18 kg

Container Information		
Package Level 1 Units		box 1 piece
Package Level 1 Width		400 mm
Package Level 1 Depth / Length		630 mm
Package Level 1 Height		300 mm
Package Level 1 Gross Weight		21.6 kg
Package Level 1 EAN		6417019416755

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 1600 A
Conventional Thermal Current (I_{the})	Fully Enclosed 1600 A
Degree of Protection	Front IP00
Distance Between Phases	Standard
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
Handle Color	Black
Handle Type	Direct mounted pistol type handle
Mechanical Durability	6000
Mounting Type	Base mounting
Number of Poles	4P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 48 W
Rated Conditional Short-Circuit Current (I_{nc})	(1250 A fuse, 415 V) 80 kA (1250 A fuse, 500 V) 100 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 1600 A (500 V) 1600 A (690 V) 1600 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 1600 A (500 V) 1600 A (690 V) 1600 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 1250 A (500 V) 1250 A (690 V) 1250 A
Rated Operational Power AC-23A (P_e)	(400 ... 415 V) 710 kW (500 V) 900 kW (690 V) 1200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 92 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 50 kA
Special Functions	No
Standards	IEC 60947-3
Switches Operating Mechanism	Mechanism at the End of the Switch 04 (Left Side)
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 50 ... 75 N·m

Technical UL/CSA

Tightening Torque	acc. IEC 60947-1 50 ... 75 N·m
-------------------	--------------------------------

Certificates and Declarations

A2L Certificate – IEC	1SCC301338D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301155D2704
DNV GL Certificate	1SCC301184D0203
UL Certificate	No certification needed
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122221
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3660819

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

