

LOC	DIST	REVISIONS				
CM	00	P	LTR	DESCRIPTION	DATE	DWN
			L	REVISED PER ECO-09-025490	17NOV09	MS

- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2






WIRE RANGE: 0.5-2mm² [20-14 AWG]
INSULATION RANGE: 3.30-5.08 [.130-.200] DIA.
- 3


DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

LETTER "P" STAMPED IN THIS LOCATION.
- 5

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.

4	GOLD	5	0.30 [.012] PH BRZ	1-770005-1
	GOLD	5	0.30 [.012] BRASS	1-770005-0
4	GOLD	1	0.30 [.012] PH BRZ	770005-4
4	PRE-TIN		0.30 [.012] PH BRZ	770005-3
	GOLD	1	0.30 [.012] BRASS	770005-2
	PRE-TIN		0.30 [.012] BRASS	770005-1
FINISH		MATERIAL		PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	S. CARPENTER		20MAY03		 Tyco Electronics Corporation Harrisburg, PA 17105-3608																
				CHK	C. JONES		20MAY03																		
DIMENSIONS: mm [INCHES]				TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD		C. JONES		20MAY03		NAME											
								PRODUCT SPEC		—		PIN, UNIVERSAL MATE-N-LOK(TM) II													
				0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —				APPLICATION SPEC		—															
								WEIGHT		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO							
MATERIAL				FINISH				A2		00779		C=770005		—											
SEE TABLE				SEE TABLE				CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1		REV		L	