



## Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part category	Lighting accessory
Accessory / separate part type	Super bright LED
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
Signalling colour	Blue
[Us] rated supply voltage	24 V AC/DC
Luminance	900 cd/m <sup>2</sup>
Sale per indivisible quantity	1

## Complementary

Net weight	0.009 kg
------------	----------

## Packing Units

Package 1 Weight	0.014 kg
------------------	----------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

### Contractual warranty

Warranty	18 months
----------	-----------