

Siemens  
EcoTech



solid-state contactor 1-pole 3RF33 AC-1 10 A 40 °C / 48-600 V / 24 V DC / spring-loaded terminal



|                                                         |                                                                                                                                                                                                                        |
|---------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| product brand name                                      | SIRIUS                                                                                                                                                                                                                 |
| product designation                                     | solid-state contactor                                                                                                                                                                                                  |
| product type designation                                | 3RF33                                                                                                                                                                                                                  |
| manufacturer's article number                           |                                                                                                                                                                                                                        |
| • _3 of the accessories that can be ordered             | <a href="#">3RF3900-0EA18</a>                                                                                                                                                                                          |
| product designation                                     |                                                                                                                                                                                                                        |
| • _3 of the accessories that can be ordered             | converter                                                                                                                                                                                                              |
| General technical data                                  |                                                                                                                                                                                                                        |
| product function                                        | zero-point switching                                                                                                                                                                                                   |
| product feature                                         | high blocking voltage                                                                                                                                                                                                  |
| power loss [V·A] maximum                                | 9.4 VA                                                                                                                                                                                                                 |
| power loss [W] for rated value of the current           |                                                                                                                                                                                                                        |
| • at AC in hot operating state                          | 8.5 W                                                                                                                                                                                                                  |
| • at AC in hot operating state per pole                 | 8.5 W                                                                                                                                                                                                                  |
| • without load current share typical                    | 0.4 W                                                                                                                                                                                                                  |
| type of calculation of power loss current-dependent     | linear                                                                                                                                                                                                                 |
| insulation voltage rated value                          | 600 V                                                                                                                                                                                                                  |
| degree of pollution                                     | 3                                                                                                                                                                                                                      |
| surge voltage resistance of main circuit rated value    | 6 kV                                                                                                                                                                                                                   |
| protection class IP                                     | IP20                                                                                                                                                                                                                   |
| protection class IP on the front according to IEC 60529 | IP20                                                                                                                                                                                                                   |
| shock resistance according to IEC 60068-2-27            | 15 g / 11 ms                                                                                                                                                                                                           |
| vibration resistance according to IEC 60068-2-6         | 2 g                                                                                                                                                                                                                    |
| reference code according to IEC 81346-2                 | Q                                                                                                                                                                                                                      |
| Substance Prohibitance (day/month/year)                 | 01/15/2024                                                                                                                                                                                                             |
| SVHC substance name                                     | Lead monoxide (lead oxide) CAS-No. 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5<br>Melamine CAS-No. 108-78-1<br>Dibutylbis(pentane-2,4-dionato-O,O')tin CAS-No. 22673-19-4 |
| Net Weight                                              | 0.12 kg                                                                                                                                                                                                                |
| Main circuit                                            |                                                                                                                                                                                                                        |
| number of poles for main current circuit                | 1                                                                                                                                                                                                                      |
| number of NO contacts for main contacts                 | 1                                                                                                                                                                                                                      |
| number of NC contacts for main contacts                 | 0                                                                                                                                                                                                                      |
| type of voltage of the operating voltage                | AC                                                                                                                                                                                                                     |
| operating voltage                                       |                                                                                                                                                                                                                        |

|                                                                                                                                                                                                                                                                                                 |                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at AC <ul style="list-style-type: none"> <li>— at 50 Hz rated value</li> <li>— at 60 Hz rated value</li> </ul> </li> </ul>                                                                                                                             | 48 ... 600 V<br>48 ... 600 V                                                                                |
| <b>operating frequency rated value</b>                                                                                                                                                                                                                                                          | 50 ... 60 Hz                                                                                                |
| <b>relative symmetrical tolerance of the operating frequency</b>                                                                                                                                                                                                                                | 10 %                                                                                                        |
| <b>operating range relative to the operating voltage at AC</b> <ul style="list-style-type: none"> <li>• at 50 Hz</li> <li>• at 60 Hz</li> </ul>                                                                                                                                                 | 40 ... 660 V<br>40 ... 660 V                                                                                |
| <b>operational current rated value maximum</b>                                                                                                                                                                                                                                                  | 10 A                                                                                                        |
| <b>operational current</b> <ul style="list-style-type: none"> <li>• at AC-1 at 400 V rated value</li> <li>• at AC-51 rated value</li> <li>• at AC-51 according to IEC 60947-4-3</li> <li>• according to UL 508 rated value</li> </ul>                                                           | 10 A<br>10 A<br>10 A<br>8 A                                                                                 |
| <b>ampacity maximum</b>                                                                                                                                                                                                                                                                         | 10 A                                                                                                        |
| <b>operational current minimum</b>                                                                                                                                                                                                                                                              | 100 mA                                                                                                      |
| <b>rate of voltage rise at the thyristor for main contacts maximum permissible</b>                                                                                                                                                                                                              | 1 000 V/μs                                                                                                  |
| <b>blocking voltage at the thyristor for main contacts maximum permissible</b>                                                                                                                                                                                                                  | 1 600 V                                                                                                     |
| <b>reverse current of the thyristor</b>                                                                                                                                                                                                                                                         | 10 mA                                                                                                       |
| <b>derating temperature</b>                                                                                                                                                                                                                                                                     | 40 °C                                                                                                       |
| <b>surge current resistance rated value</b>                                                                                                                                                                                                                                                     | 260 A                                                                                                       |
| <b>I<sup>2</sup>t value maximum</b>                                                                                                                                                                                                                                                             | 360 A <sup>2</sup> ·s                                                                                       |
| <b>Control circuit/ Control</b>                                                                                                                                                                                                                                                                 |                                                                                                             |
| <b>type of voltage of the control supply voltage</b>                                                                                                                                                                                                                                            | DC                                                                                                          |
| <b>control supply voltage at DC</b>                                                                                                                                                                                                                                                             | 15 ... 24 V                                                                                                 |
| <b>control supply voltage 1 at DC rated value</b>                                                                                                                                                                                                                                               | 24 V                                                                                                        |
| <b>control supply voltage at DC</b> <ul style="list-style-type: none"> <li>• initial value for signal &lt;1&gt; detection</li> <li>• full-scale value for signal&lt;0&gt; recognition</li> </ul>                                                                                                | 15 V<br>5 V                                                                                                 |
| <b>operating range factor control supply voltage rated value at DC</b> <ul style="list-style-type: none"> <li>• initial value</li> <li>• full-scale value</li> </ul>                                                                                                                            | 0.63<br>1                                                                                                   |
| <b>control current at minimum control supply voltage</b> <ul style="list-style-type: none"> <li>• at DC</li> </ul>                                                                                                                                                                              | 13 mA                                                                                                       |
| <b>control current at DC rated value</b>                                                                                                                                                                                                                                                        | 15 mA                                                                                                       |
| <b>ON-delay time</b>                                                                                                                                                                                                                                                                            | 1 ms; additionally max. one half-wave                                                                       |
| <b>OFF-delay time</b>                                                                                                                                                                                                                                                                           | 1 ms; additionally max. one half-wave                                                                       |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                                                       |                                                                                                             |
| <b>fastening method side-by-side mounting</b>                                                                                                                                                                                                                                                   | Yes                                                                                                         |
| <b>fastening method</b>                                                                                                                                                                                                                                                                         | screw fixing and snap-on mounting on standard mounting rail 35 mm according to IEC 60715                    |
| <b>design of the thread of the screw for securing the equipment</b>                                                                                                                                                                                                                             | M4                                                                                                          |
| <b>height</b>                                                                                                                                                                                                                                                                                   | 95 mm                                                                                                       |
| <b>width</b>                                                                                                                                                                                                                                                                                    | 22.5 mm                                                                                                     |
| <b>depth</b>                                                                                                                                                                                                                                                                                    | 89 mm                                                                                                       |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                                                   |                                                                                                             |
| <b>product component removable terminal for auxiliary and control circuit</b>                                                                                                                                                                                                                   | Yes                                                                                                         |
| <b>type of electrical connection</b> <ul style="list-style-type: none"> <li>• for main current circuit</li> <li>• for auxiliary and control circuit</li> </ul>                                                                                                                                  | spring-loaded terminals<br>spring-loaded terminals                                                          |
| <b>type of connectable conductor cross-sections</b> <ul style="list-style-type: none"> <li>• for main contacts <ul style="list-style-type: none"> <li>— solid</li> <li>— finely stranded with core end processing</li> <li>— finely stranded without core end processing</li> </ul> </li> </ul> | 2x (0.5 ... 2.5 mm <sup>2</sup> )<br>2x (0.5 ... 1.5 mm <sup>2</sup> )<br>2x (0.5 ... 2.5 mm <sup>2</sup> ) |

|                                                                                               |                                                                       |
|-----------------------------------------------------------------------------------------------|-----------------------------------------------------------------------|
| • for AWG cables for main contacts                                                            | 2x (18 ... 14)                                                        |
| <b>connectable conductor cross-section for main contacts</b>                                  |                                                                       |
| • solid or stranded                                                                           | 0.5 ... 2.5 mm <sup>2</sup>                                           |
| • finely stranded with core end processing                                                    | 0.5 ... 1.5 mm <sup>2</sup>                                           |
| • finely stranded without core end processing                                                 | 0.5 ... 2.5 mm <sup>2</sup>                                           |
| <b>type of connectable conductor cross-sections</b>                                           |                                                                       |
| • for auxiliary and control contacts                                                          |                                                                       |
| — solid                                                                                       | 0.5 ... 1.5 mm <sup>2</sup>                                           |
| — finely stranded with core end processing                                                    | 0.5 ... 2.5 mm <sup>2</sup>                                           |
| — finely stranded without core end processing                                                 | 0.5 ... 2.5 mm <sup>2</sup>                                           |
| • for AWG cables for auxiliary and control contacts                                           | 1x (20 ... 12)                                                        |
| <b>AWG number as coded connectable conductor cross section for main contacts</b>              | 18 ... 14                                                             |
| <b>stripped length of the cable</b>                                                           |                                                                       |
| • for main contacts                                                                           | 10 mm                                                                 |
| • for auxiliary and control contacts                                                          | 10 mm                                                                 |
| <b>type of grounding</b>                                                                      | grounding by snapping onto grounded DIN rails                         |
| <b>UL/CSA ratings</b>                                                                         |                                                                       |
| <b>operational current according to UL 508 rated value</b>                                    | 8 A                                                                   |
| Electrical Safety                                                                             |                                                                       |
| <b>touch protection on the front according to IEC 60529</b>                                   | finger-safe, for vertical contact from the front                      |
| <b>Ambient conditions</b>                                                                     |                                                                       |
| installation altitude at height above sea level maximum                                       | 1 000 m                                                               |
| <b>ambient temperature</b>                                                                    |                                                                       |
| • during operation                                                                            | -25 ... +60 °C                                                        |
| • during storage                                                                              | -55 ... +80 °C                                                        |
| <b>Electromagnetic compatibility</b>                                                          |                                                                       |
| <b>conducted interference</b>                                                                 |                                                                       |
| • due to burst according to IEC 61000-4-4                                                     | 2 kV / 5 kHz, behavior criterion 2                                    |
| • due to conductor-earth surge according to IEC 61000-4-5                                     | 2 kV, behavior criterion 2                                            |
| • due to conductor-conductor surge according to IEC 61000-4-5                                 | 1 kV, behavior criterion 2                                            |
| • due to high-frequency radiation according to IEC 61000-4-6                                  | 140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1 |
| <b>field-based interference according to IEC 61000-4-3</b>                                    | 80 MHz ... 1 GHz 10 V/m, behavior criterion 1                         |
| <b>electrostatic discharge according to IEC 61000-4-2</b>                                     | 4 kV contact discharging / 8 kV air discharging, behavior criterion 2 |
| <b>conducted HF interference emissions according to CISPR11</b>                               | Class A for industrial environment                                    |
| <b>field-bound HF interference emission according to CISPR11</b>                              | Class B for the domestic, business and commercial environments        |
| <b>Short-circuit protection, design of the fuse link</b>                                      |                                                                       |
| manufacturer's article number                                                                 |                                                                       |
| • of full range R fuse link for semiconductor protection at NH design usable                  | <a href="#">3NE8714-1</a>                                             |
| • of gS fuse for semiconductor protection at NH design usable                                 | <a href="#">3NE1813-0</a>                                             |
| • of back-up R fuse link for semiconductor protection at NH design usable                     | <a href="#">3NE8810-0MK</a>                                           |
| • of back-up R fuse link for semiconductor protection at cylindrical design 10 x 38 mm usable | <a href="#">3NC1032</a>                                               |
| • of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable | <a href="#">3NC1440</a>                                               |
| • of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable | <a href="#">3NC2240</a>                                               |
| manufacturer's article number of the gG fuse                                                  |                                                                       |
| • at NH design usable                                                                         | <a href="#">3NA6803-6</a>                                             |
| <b>Approvals Certificates</b>                                                                 |                                                                       |
| <b>Environment</b>                                                                            | <b>General Product Approval</b>                                       |

[Environmental Conformations](#)



Siemens  
EcoTech



|     |                   |       |
|-----|-------------------|-------|
| EMV | Test Certificates | other |
|-----|-------------------|-------|



[Type Test Certificates/Test Report](#)

[Confirmation](#)



[Confirmation](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF3310-2AA06>

##### Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF3310-2AA06>



##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RF3310-2AA06>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RF3310-2AA06&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF3310-2AA06&lang=en)





last modified:

7/11/2026