




Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 928960-2
POS-LOCK STECKH 6,3



TE Part # 160914-4
FF 250 REC 4-6MM2 TPPB



TE Part # 160914-2
FF 250 REC 4-6MM2 TPBR



TE Part # 160914-3
250 FASTIN FASTON,REC.,12-10 AWG, PB



TE Part # 928950-2
FF 250 TAB 2.5-4.0 MM2 TP CUSN4




TE Part # 928958-8
PL REC 2.5-4.0 MM2 0.40 X 52.32 SP



TE Part # 928959-7
POS-LOCK STECKH 6,3

Customers Also Bought



TE Part #969005-2
MT2 A REC 1.6 Contact SWS Sn



TE Part #1-1718484-1
CARRIER FOR RECEPTACLE INSERTS



TE Part #794281-1
15P UMNL INTERFACE SEAL



TE Part #2820193040
44A0111-18-9





TE Part #HDP24-18-14SE-L017
REC, 14P, BLK, E, RNG, 16, S



TE Part #211398-2
CPC RECPT. SIZE 13-7



TE Part #2-179552-4
DYNAMIC D-3200S TAB HSG 4P K/Y



TE Part #2600023-1
2CCT BLACK PLUG W/SMALL SEAL

TE Part #1SNS420099Z0000
XUKHD201019 -3EER400027-6354-TBL-NCBrIfp



TE Part #344271-1
3 WAY TAB HOUSING BLACK ECONO

Documents

Product Drawings

DIE F6.3FF REC.

English

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (non U.S.)

German