



**Part Number :** [936000032](#)

**Product Description :** Heavy-Duty Metal Gable Gland - 5 Bar, for 24.00-38.00mm Cable, M50x1.5 Thread

**Series Number :** 93600

**Status :** Active

**Product Category :** Heavy-Duty Cable Glands

**Engineering Number :** 7000.6835.0



---

## Documents & Resources

### Drawings

[936000032\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Gable Gland - 5 Bar, for 24.00-38.00mm Cable, M50x1.5 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191824345

### Physical

Cable Diameter	24.00-38.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	304.000/g
Packaging Type	Bag
Panel Cutout Diameter	50.50mm
Temperature Range - Operating	-40° to +125°C
Thread Size	M50x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	Industrial connector hoods and housings