


## FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical stress
- **3 Cores:** Suitable for three-phase power applications
- **Operating Temperature Range -15 °C to 90 °C:** Ensures performance in diverse environmental conditions
- **Voltage Rating 500 V:** Suitable for a wide range of electrical applications
- **Plain Conductor Type:** Simplifies installation and connection processes
- **50 m Length:** Provides ample cable for extensive installations

## RS PRO 1.5 mm<sup>2</sup> Flexible Cable, 50 m Annealed Copper

RS Stock No: 606-114



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial environments. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is ideal for applications requiring flexibility and resilience, making it suitable for installations where space is limited or movement is frequent.

## General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

## Mechanical Specifications

Cable CSA	1.5 mm <sup>2</sup>
Cable Length	50 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	9.4 mm

## Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

## Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

## Electrical Specifications

Voltage	500 V
---------	-------