

EMG725


GANT DE PROTECTION CONTRE LES COUPURES DE NIVEAU B / A2 ENDUCTION PU

Gant léger, souple et confortable, résistant aux coupures, enduit PU.
Idéal pour la manipulation de pièces tranchantes dans des conditions sèches ou grasses.

CARACTERISTIQUES

- Résistance à la coupure: niveau B / A2
- Gant souple et confortable offrant une grande dextérité
- L'absence de fibres de verre et d'acier réduit les risques d'irritation
- L'enduction de la paume en polyuréthane assure une bonne protection contre l'abrasion
- Renfort pouce index pour une meilleure durabilité
- Conçu pour un mouvement facile et un port continu
- Dos de la main respirant pour réduire la transpiration
- Le tricot sans couture évite les irritations
- Poignet élastiqué pour un bon maintien

CERTIFICATION



INDUSTRIES & APPLICATIONS

Industries

Aerospace
Engineering

Logistique
Construction

Applications

Assemblage
Manutention

Maintenance
Mécanique de Precision

EMG725

INFORMATION PRODUIT

MATERIAU	TRICOT:	Jauge 13 HPPE, nylon
	ENDUCTION:	Polyurethane
COULEUR	Gris/Noir	
LONGUEUR (mm)	250 (variable selon taille)	
POIGNET	Poignet élastiqué	

ORDERING INFORMATION

SIZE	CODE	PACKAGING
6/XS 7/ S	EMG00725FB EMG00725FD	10 pairs per bag
9/L 10/XL	EMG00725FH EMG00725FJ	120 pairs per case
12/XXXL	EMG00560EN	

RECOMMENDATIONS FOR USE

USE: General handling glove with cut protection. Not suitable for thermal, electrical and chemical protection. Do not use near moving machines if there is a risk of entanglement.

STORAGE: Store in dry conditions in the original packaging and away from direct sunlight.


CLEANING: To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present.

LIFETIME: Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use.

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016
PERFORMANCE LEVELS*



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

ANSI/ISEA 105-2016 ABRASION RATING CHART

Abrasion Level Rating	0	1	2	3	4	5	6
Gram Load	500	500	500	500	1000	1000	1000
Abrasion Cycles to Fail	<100	≥100	≥500	≥1,000	≥3,000	≥10,000	≥20,000

CLASSIFICATION FOR CUT RESISTANCE

Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A4	≥ 1500
A5	≥ 2200
A7	≥ 4000
A8	≥ 5000

ANSI/ISEA PUNCTURE RESISTANCE

ANSI Puncture Level	Puncture Resistance (newtons)
1	10-19
2	20-59
4	100-149
5	150+

Puncture Resistance (ANSI/ISEA 105): Puncture resistance is determined by the max force that it takes, exerted from a probe, to puncture the fabric.