

# Manifold sub-base VABV-S1-1HSB-G38

Part number: 8030650

**FESTO**



 [General operating condition](#)

## Data sheet

| Feature                            | Value                                                                                      |
|------------------------------------|--------------------------------------------------------------------------------------------|
| Construction width                 | 44 mm                                                                                      |
| Exhaust-air function               | Can be throttled                                                                           |
| Based on standard                  | ISO 5599-1                                                                                 |
| Max. number of valve positions     | 1                                                                                          |
| Operating pressure                 | -0.09 MPa ... 1 MPa                                                                        |
| Operating pressure                 | -0.9 bar ... 10 bar                                                                        |
| Suitability for vacuum             | Yes                                                                                        |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC     | 0 - No corrosion stress                                                                    |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L                                                                          |
| Storage temperature                | -20 °C ... 60 °C                                                                           |
| Media temperature                  | -10 °C ... 50 °C                                                                           |
| Pilot medium                       | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Ambient temperature                | -10 °C ... 50 °C                                                                           |
| Product weight                     | 490 g                                                                                      |
| Pneumatic connection, port 2       | G3/8                                                                                       |
| Pneumatic connection, port 4       | G3/8                                                                                       |
| Note on materials                  | RoHS compliant                                                                             |
| Material sub-base                  | Die-cast aluminium                                                                         |