


High Frequency and High Power Thin Film Chip Resistor



FEATURES

- Operating frequency up to 50 GHz
- Thin film microwave resistors
- Flip chip or wraparound terminals available
- Ohmic range: 20 Ω to 120 Ω
- High power (up to 2.8 W for 0603 size) - no active cooling required (see specification)
- Small internal reactance (LC down to 1×10^{-24})
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

HALOGEN FREE
Available

GREEN (5-2008)
Available

LINKS TO ADDITIONAL RESOURCES



Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

These miniaturized components are designed to minimize internal reactance. When correctly mounted, they function across a wide frequency band, up to 50 GHz for CHEP0402 and 40 GHz for CHEP0603 from 20 Ω to 120 Ω . Aluminum nitride substrate combined with PCB dissipation ensures high power capability. The resistive thin film layer can withstand an established temperature as high as 250 °C.

STANDARD ELECTRICAL SPECIFICATIONS						
MODEL	SIZE	RESISTANCE RANGE Ω	RATED POWER ⁽¹⁾ P_n W	LIMITING ELEMENT VOLTAGE V	TOLERANCE \pm %	TEMPERATURE COEFFICIENT \pm ppm/°C
CHEP0402	0402	20 to < 50	1.2 (1.8)	37	2, 5	100 (50 upon request)
	0402	50 to \leq 120	1.2 (1.8)	37	1, 2, 5	100 (50 upon request)
CHEP0603	0603	20 to < 50	2.0 (2.8)	50	2, 5	100 (50 upon request)
	0603	50 to \leq 120	2.0 (2.8)	50	1, 2, 5	100 (50 upon request)


Note

⁽¹⁾ Higher power in parenthesis achievable under additional conditions - see High Power Capability

MECHANICAL SPECIFICATIONS	
Substrate	Aluminum nitride
Technology	Thin film
Film	Nickel chromium-based alloy with mineral passivation
Protection	Epoxy + silicone
Terminations	F, N type: tin silver over nickel barrier G type: gold over nickel barrier

CLIMATIC SPECIFICATIONS	
Operating temperature range	-55 °C to +155 °C

POWER DERATING CURVE ⁽¹⁾



Note

⁽¹⁾ FR4 PCB with one side 70 μ m thick copper, width 1 cm for 0402 and 2 cm for 0603 SnAgCu solder paste

DIMENSIONS in millimeters (inches)					
CHEP0402F / CHEP0603F			CHEP0402N / CHEP0402G / CHEP0603N / CHEP0603EPG		
CASE SIZE MODEL	DIMENSIONS				
	A ± 0.10 (± 0.004)	B ± 0.10 (± 0.004)	C ± 0.127 (± 0.005)	D E (WHEN APPLICABLE)	
				MIN.	MAX.
CHEP0402F CHEP0402N CHEP0402G	1.000 (0.040)	0.600 (0.023)	0.500 (0.020)	0.150 (0.006)	0.350 (0.014)
CHEP0603F CHEP0603N CHEP0603G	1.520 (0.060)	0.850 (0.033)	0.500 (0.020)	0.250 (0.010)	0.510 (0.020)

PERFORMANCES			
TEST ⁽¹⁾	CONDITIONS	GLOBAL PERFORMANCES	TYPICAL PERFORMANCES
Temperature cycling	JESD22-A104 1000 cycles (-55 °C to +155 °C)	± 0.2 %	± 0.08 %
Storage	MIL-STD-202 method 108 +155 °C unpowered	± 0.2 %	± 0.08 %
Operational life	MIL-STD-202 method 108 condition D Steady state T = 70 °C at rated power 90' on / 30' off / 1000 h	± 0.2 %	± 0.06 %
Biased humidity	MIL-STD-202 method 103 1000 h 85 °C / 85 % RH 10 % of operating power	± 1.0 %	± 0.6 %
Terminal strength	AEC-Q200-006	± 0.1 %	± 0.05 %
Solderability	J-STD-002 Method B1 245 °C SnAg 5 s Method D 260 °C SnAg 30 s	Good tinning (≥ 95 % covered) No visible damage	

ASSEMBLY SPECIFICATION			
FOR THE ASSEMBLY ON BOARD, WE RECOMMEND THE LEAD (Pb)-FREE THERMAL PROFILE AS PER J-STD-020C			
TEST ⁽¹⁾	CONDITIONS	GLOBAL PERFORMANCES	TYPICAL PERFORMANCES
Resistance to soldering heat	MIL-STD-202 method 210 condition K Flux above 217 °C 60 s to 150 s	± 0.03 %	± 0.02 %
Boardflex	AEC-Q200-005	± 0.1 %	± 0.06 %


Note
⁽¹⁾ According to AEC-Q200 rev. E

LAND PATTERN FOR F “FLIP CHIP” TERMINATIONS in millimeters (inches)			
CHIP SIZE	Z _{max.}	X _{max.}	G _{min.}
0402	1.40 (0.055)	0.65 (0.026)	0.40 (0.016)
0603	1.71 (0.067)	0.90 (0.035)	0.76 (0.030)

Note

- Suggested land pattern: according to IPC-7351

LAND PATTERN FOR N AND G WRAPAROUND TERMINATIONS in millimeters (inches)			
CHIP SIZE	Z _{max.}	X _{max.}	G _{min.}
0402	1.55 (0.061)	0.73 (0.029)	0.15 (0.006)
0603	2.37 (0.093)	0.98 (0.039)	0.35 (0.014)

HIGH POWER CAPABILITY (1)


SIZE	RATED HIGH POWER W <i>P_{hp}</i>
0402	1.8
0603	2.8

Note

- (1) Polyimide PCB with one side 70 μm thick copper, width 1 cm for 0402 and 2 cm for 0603 solder paste PbSnAg

PERFORMANCES WITH HIGH POWER RATING <i>P_{hp}</i>			
TESTS	CONDITIONS	GLOBAL PERFORMANCES	TYPICAL PERFORMANCES
Operational life	MIL-STD-202 method 108 condition D Steady state T = 70 °C at rated power 90' on / 30' off / 1000 h	± 0.2 %	± 0.1 %

PACKAGING					
SIZE	MOQ ⁽¹⁾	NUMBER OF PIECES PER PACKAGE			TAPE WIDTH
		WAFFLE PACK 2" x 2"	TAPE AND REEL (CODE DEPENDENT)		
			MIN.	MAX.	
0402	100 for waffle pack	100	100	5000	8 mm
0603					

Notes

- Standard packaging is plastic tape and reel for all sizes
- Waffle pack is available for all sizes
- ⁽¹⁾ See "Codification of Packaging" table for tape and reel mins

GLOBAL PART NUMBER INFORMATION																
Global Part Numbering: CHEP0402-100RJTF																
C	H	E	P	0	4	0	2	-	1	0	0	R	J	F	T	F
GLOBAL MODEL		SIZE		OHMIC VALUE			TOLERANCE			TERMINATION			PACKAGING			
CHEP		0402 0603		20R to 120R			F = 1 % G = 2 % J = 5 %			F (flip chip): SnAg over nickel barrier N (W/A): SnAg over nickel barrier G (W/A): gold over nickel barrier			For more information see Codification of Packaging table			


CODIFICATION OF PACKAGING	
WAFFLE PACK (available for all sizes)	
W	100 min., 1 mult.; 100 pcs max.
PLASTIC TAPE (standard packaging for all sizes)	
T	100 min., 100 mult.; delivered in reels of 1000 pcs max.
TD	1000 min., 1000 mult.; delivered in reels of 1000 pcs
TF	5000 min., 5000 mult.; delivered in reels of 5000 pcs

TYPICAL HIGH FREQUENCY PERFORMANCE ELECTRICAL MODEL	
C	Internal shunt capacitance
L	Internal inductance
R	Resistance
Z	Internal impedance (R, L, C)
L _c	External connection inductance
C _g	External capacitance to ground


The test board used to collect data respect the electrical model. Test board was designed to reduce reflection and measurement noise at high frequency. The reference plane is at the pad of the component.



INTERNAL IMPEDANCE CURVES




Internal impedance curve for 0402 size (F termination)




Internal impedance curve for 0402 size (N and G terminations)



INTERNAL IMPEDANCE CURVES



Internal impedance curve for 0603 size (F termination)





Internal impedance curve for 0603 size (N and G terminations)





S-PARAMETER

CHEP0402 (F Termination) 50 Ω and 100 Ω





CHEP0402 (N and G Terminations) 50 Ω and 100 Ω







S-PARAMETER

CHEP0603 (F Termination) 50 Ω and 100 Ω



CHEP0603 (N and G Terminations) 50 Ω and 100 Ω





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.