



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous




materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 480142-2 HSG AMP LEAF 22 POS</p>	 <p>TE Part # 583680-1 HSG AMP LEAF 15 POS</p>	 <p>TE Part # 583989-3 CONT AMP LEAF L/P 30/3 AU</p>	 <p>TE Part # 583204-2 CONT AMP LF</p>
 <p>TE Part # 182029-2 AMP LEAF CTC L.P. 22-18</p>	 <p>TE Part # 280623-2 AMP LEAF CTC 22-18 AWG</p>	 <p>TE Part # 583617-1 HSG AMP LEAF 22 POS</p>	 <p>TE Part # 1-583989-2 AMP LEAF STRIP PLT</p>
 <p>TE Part # 1-583989-3 AMP LEAF STRIP PLT</p>	 <p>TE Part # 1-583989-6 AMP LEAF STRIP PLT</p>	 <p>TE Part # 1-583990-3 AMP LF CONT STRIP</p>	 <p>TE Part # 1-583990-4 AMP LF CONT STRIP</p>
 <p>TE Part # 1-583990-5 CONTACT AMP LEAF 15 AU</p>	 <p>TE Part # 1-583990-6 CONTACT AMP LEAF 30 AU</p>	 <p>TE Part # 42840-3 CONT AMP LEAF L/P 30/3 AU</p>	 <p>TE Part # 582140-5 HSG AMP LEAF 8 POS</p>







TE Part # 583989-1
AMP LEAF STRIP TERM.



TE Part # 583989-4
CONT AMP LEAF L/P 15/3 AU




TE Part # 583990-1
AMP LEAF STRIP TERM




TE Part # 583990-3
CONT AMP LEAF L/P 30/3 AU


Customers Also Bought




TE Part #1487588-2
USB, A-B, 28/24, WHITE, 1.5M




TE Part #1-1625892-8
3W SM M/OX 5% 180K




TE Part #1-965426-1
FLACHSTE-GEH2,8 6P




TE Part #1-962915-1
TAB 2.8x0.8 CONTACT CS SWS Sn




TE Part #1579008-5
EXTRACTION TOOL




TE Part #K1008489
Emergency Power Switch Type 24-34-02



TE Part #539723-2
DIE-MCP-2,8/1,5-4MM



TE Part #1SNA115409R2600
MB4/6.L5



TE Part #1-963748-1
TAB 2.8x0.8 CONTACT CF SWS Sn (LP)

Documents

- Product Drawings

AMP-LEAF EXTRACTION TOOL

English
- Instruction Sheets

Instruction Sheet (U.S.)

English
- AMP-LEAF Extraction Tools

English

