




LED Spot PAR16 Switch GU10 DIM 4.8W (65W) 450lm 827-865 38°

Article number: 147213

BAI BaiSpot LED Spot PAR16 Switch GU10 DIM 4.8W (65W) 450lm 3CCT 2700K 4000K 6500K 38°
GlassReflector 230V 50x56mm LED-Lamp

Discover the versatility of the Baispot series with this dimmable LED Spot PAR16 Switch. This innovative reflector lamp combines sustainability, flexibility, and ease of use in one smart lighting solution. Sustainable lighting is about more than simply replacing traditional light sources with energy-efficient alternatives. Thanks to the unique Switch technology, you get three colour temperatures in a single product. With a simple switch adjustment, you can easily choose between extra warm 2200K ambience, comfortable 2700K lighting, or bright functional 4000K light. By combining three versions into one lamp, you not only save energy, but also reduce transport, storage, and inventory costs. That's true "Smart & Green Thinking". Suitable for ambient temperatures ranging from -20°C to +40°C and perfect for homes, retail spaces, hospitality environments, and offices.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	LED Spot PAR16 Switch GU10 DIM 4.8W (65W) 450lm 827-865 38°
Brand	Bailey
Productseries	BaiSpot LED MV PAR16
Producttype	PAR16 GU10 827-865 38D

ETIM specifications

Socket	GU10
Luminous flux [lm]	450 - 450
Nominal voltage [V]	220 - 240
Lamp power [W]	4.8 - 4.8
Colour temperature [K]	2700 - 6500
Diameter [mm]	50
Length [mm]	56
Dimmable	Yes
Lamp shape	Reflector
Beam angle [°]	38 - 38
Colour	White
Type of glass/cover	Prism
Lamp designation	PAR16
Colour rendering index CRI	80-89
Voltage type	AC
Filament lamp	No
Luminous intensity [cd]	650
Rated luminous flux according to IEC 62612 [lm]	450
Power factor	0.8
Lamp efficacy [lm/W]	94
Nominal current [mA]	30 - 30
Colour of light according to EN 12464-1	Warm white < 3300 K
Housing colour	Colourless
Average nominal lifetime [h]	20000
Degree of protection (IP)	IP20
Colour consistency (McAdam ellipse)	SDCM6
Min. number of switching cycles	10000
Weighted energy consumption in 1000 hours [kWh]	5
Remote operation possible	No
With movement sensor	No
With remote control	No
Photobiological safety according to EN 62471	RG0
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for electronic ballast	No
Suitable for magnetic ballast	No
Dimming phase cut-off (trailing edge)	Yes
Dimming phase cut-on (leading edge)	Yes
Dimming Touch and Dim	No

Dimming Zigbee	No
Dimming Bluetooth	No
Dimming Wi-Fi	No
Energy efficiency class according to EU regulation 2019/2015	E
With twilight switch	No
Material of light bulb	Glass

Alternative articles



146952

LED PAR16 WarmDim GU10
3.6W (50W) 345lm 827-818 36°

Complementary articles



144262

Spot GU10 Set Alu Black Fixed

144263

Spot GU10 Set Alu Black
Adjustable