



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

Rubson Mastic SP2 UNI, All colours

SDS No. : 677767
V001.0

Revision: 08.01.2020
printing date: 25.06.2020
Replaces version from: -

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Rubson Mastic SP2 UNI, All colours

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Joint sealant, silicone

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information

Contains: N,N-Dimethyl-3-(trimethoxysilyl)propylamine May produce an allergic reaction.

Precautionary statement:

P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.
P262 Do not get in eyes, on skin, or on clothing.
P271 Use only outdoors or in a well-ventilated area.

2.3. Other hazards

Evolves methanol during cure.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Joint sealants

Base substances of preparation:

Polydimethyl siloxane

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	265-148-2	1- < 3 %	Asp. Tox. 1 H304
N,N-Dimethyl-3- (trimethoxysilyl)propylamine 2530-86-1	219-786-3 01-2120753783-46	0,1- < 1 %	Eye Dam. 1 H318 Skin Sens. 1B H317

For full text of the H - statements and other abbreviations see section 16 "Other information".**Substances without classification may have community workplace exposure limits available.****SECTION 4: First aid measures****4.1. Description of first aid measures**

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water, seek medical advice if necessary.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.

Ensure adequate ventilation.

Avoid contact with skin and eyes.

Danger of slipping on spilled product.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Ensure that workrooms are adequately ventilated.

Avoid skin and eye contact.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, frost-free place.

Store in a dry place.

Temperatures between 0 °C and + 30 °C

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Joint sealant, silicone

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Methanol 67-56-1 [METHANOL]	250	333	Short Term Exposure Limit (STEL):		EH40 WEL
Methanol 67-56-1 [METHANOL]			Skin designation:	Can be absorbed through the skin.	EH40 WEL
Methanol 67-56-1 [METHANOL]	200	266	Time Weighted Average (TWA):		EH40 WEL
Methanol 67-56-1 [METHANOL]	200	260	Time Weighted Average (TWA):	Indicative	ECTLV

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, TOTAL		6	Time Weighted Average (TWA):		IR_OEL

INHALABLE DUST]					
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Distillates (petroleum), hydrotreated middle 64742-46-7 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Methanol 67-56-1 [METHANOL]	200	260	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Methanol 67-56-1 [METHANOL]			Skin designation:	Can be absorbed through the skin.	IR_OEL
Methanol 67-56-1 [METHANOL]	200	260	Time Weighted Average (TWA):	Indicative	ECLTV

Biological Exposure Indices:

None

8.2. Exposure controls:**Respiratory protection:**

The product should only be used at workplaces with intensive ventilation/extraction. If intensive ventilation/extraction is not possible then self-contained independent respiratory protection should be worn.

Hand protection:

Recommended are gloves made from Nitril rubber (Material thickness >0,1 mm, Perforation time < 30s).Gloves should be replaced after each short time contact or contamination. Available at laboratory specialized trade or at pharmacies / chemist's shops.

Eye protection:

Goggles which can be tightly sealed.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste pasty varied, according to coloration
Odor	neutral
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density	1,42 g/cm ³

(20 °C (68 °F))	
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	Insoluble
(23 °C (73.4 °F); Solvent: Water)	
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

Evolves methanol during cure.

SECTION 11: Toxicological information**General toxicological information:**

An allergic reaction cannot be excluded after repeated skin contact.

11.1. Information on toxicological effects**Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	LD50	> 5.000 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	LD50	> 2.000 mg/kg	rat	OECD Guideline 423 (Acute Oral toxicity)
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	Acute toxicity estimate (ATE)	2.500 mg/kg		Expert judgement

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	LD50	> 2.000 mg/kg	rabbit	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	LC50	> 5,266 mg/l	dust/mist	4 h	rat	not specified

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	not corrosive	4 h	Human, EpiSkinTM (SM), Reconstructed Human Epidermis (RHE)	OECD Guideline 431 (In Vitro Skin Corrosion: Reconstructed Human Epidermis (RHE) Test Method)
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	not irritating	15 min	Human, EpiSkinTM (SM), Reconstructed Human Epidermis (RHE)	OECD Guideline 439 (In Vitro Skin Irritation: Reconstructed Human Epidermis (RHE) Test Method)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	not irritating		Chicken, eye, in vitro test	OECD Guideline 438 (Isolated Chicken Eye Test Method)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
N,N-Dimethyl-3- (trimethoxysilyl)propylam ine 2530-86-1	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
N,N-Dimethyl-3-(trimethoxysilyl)propylamine 2530-86-1	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

The mixture is classified based on Viscosity data.

Hazardous substances CAS-No.	Viscosity (kinematic) Value	Temperature	Method	Remarks
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	4 mm ² /s	40 °C	not specified	

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	LC50	> 10.000 mg/l	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N,N-Dimethyl-3- (trimethoxysilyl)propylamine 2530-86-1	EC50	> 100,1 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

No data available.

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N,N-Dimethyl-3- (trimethoxysilyl)propylamine 2530-86-1	EC50	> 311 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
N,N-Dimethyl-3- (trimethoxysilyl)propylamine 2530-86-1	NOEC	32,4 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

No data available.

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Distillates (Petroleum) hydrotreated middle; Gasoil - unspecified (not cmr) 64742-46-7	not readily biodegradable.	aerobic	30 %	28 d	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)
N,N-Dimethyl-3- (trimethoxysilyl)propylamine 2530-86-1	not readily biodegradable.	aerobic	24 %	28 d	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
N,N-Dimethyl-3-(trimethoxysilyl)propylamine 2530-86-1	0,51	25 °C	QSAR (Quantitative Structure Activity Relationship)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
N,N-Dimethyl-3-(trimethoxysilyl)propylamine 2530-86-1	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080410

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0,00 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H304 May be fatal if swallowed and enters airways.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.