




TE Internal #: 1734723-6

Single Port, 1 x 1, Standard Profile, RJ Type Jacks & Plugs, Jack, Standard - Latch Down, Right Angle, Shielded, Cat 3, RJ25 Connectors

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > RJ25 Connectors



Port Configuration: **Single Port**

Port Matrix Configuration: **1 x 1**

Connector Profile: **Standard**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly
Connector System	Cable-to-Board
Grounding Options	PCB Ground
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack

Configuration Features

Number of PCB Ground Tabs	2
Number of Positions	6
Port Configuration	Single Port
Port Matrix Configuration	1 x 1
Connector Contact Density	Standard
PCB Mount Orientation	Right Angle
Number of Loaded Positions	6

Body Features

Shield Plating Material	Nickel
Shield Material	Brass
PCB Ground Tab Location	6.8 mm[.268 in]
Connector Profile	Standard



Modular Jack Latch Orientation	Standard - Latch Down
--------------------------------	-----------------------

Contact Features

Contact Underplating Material	Nickel
	15 µin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold (Au)
Contact Current Rating (Max)	1 A
PCB Contact Termination Area Plating Material	Gold

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	2.4 mm[.094 in]

Mechanical Attachment

Mating Alignment	Without
Connector Mounting Type	Board Mount
Panel Mount Feature	Without

Housing Features

Mating Entry Location	Side
Housing Color	Black
Housing Material	PA 46
Centerline (Pitch)	1.02 mm[.04 in]

Dimensions

Connector Height	11.05 mm[.435 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	Yes

Industry Standards

Performance Category	Cat 3
UL Flammability Rating	UL 94V-0

Packaging Features



Packaging Method	Tray
Packaging Quantity	120

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought







TE Part #2-1747050-1
GIC 7.92 2POS PLUG NAT KEYING C




TE Part #2-84953-8
1MM FPC HORZ.TOP CONT.ASSY 28P




TE Part #5104340-5
A/L LOW PRO HDR 24P RA HT




TE Part #1-1624112-2
3650 0402 1.0nH 10% 2K RL




TE Part #1217324-1
TAB POKE-IN MAG-MATE 18-14




TE Part #2-1586042-0
20P VAL-U-LOK R/A HDR V0




TE Part #5-146131-5
12 MODII HDR DRST SFMNT B/A LF



TE Part #646274-1
2MM HM PIN PWR/GRD MODULE



TE Part #1-640551-1
11P MTA156 COVER



TE Part #1-1734839-4
FPC CONN. 0.5MM PITCH T/C,14P

Documents

Product Drawings
RJ11,6P6C,SINGLE,DIP, 15u" Au, Reel
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1734723-6_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1734723-6_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1734723-6_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

1734723-6

Single Port, 1 x 1, Standard Profile, RJ Type Jacks & Plugs, Jack, Standard - Latch
Down, Right Angle, Shielded, Cat 3, RJ25 Connectors



Product Specification

English