



TE Internal #: 62134-2

Quick Disconnect Tab, Uninsulated, 18 – 14 AWG, .82 – 2.08 mm²

Wire, 3.56 mm [.14 in] Tab Width, F-Crimp, Straight, Steel, Nickel Plating, Strip/Reel

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **3.56 mm [.14 in]**

Mating Tab Thickness: **.41 mm [.016 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	3.56 mm[.14 in]
Mating Tab Thickness	.41 mm[.016 in]
Terminal Orientation	Straight
Contact Base Material	Steel
Terminal Plating Material	Nickel
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Packaging Features

Packaging Quantity	5500
Packaging Method	Strip/Reel

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 63701-1
[WELD TAB 20-16 AWG NPSTL](#)



TE Part # 63257-2
[CONTACT TERMINAL 22-18 AWG TPBR](#)



TE Part # 62153-1
[WELD TAB 20-16 AWG TPSTL](#)



TE Part # 7-2151875-7
[OCEAN_2.0_SPARE_PART_KIT-100F](#)



TE Part # 2151875-2
[OCEAN_2.0_Applicator-S-100FA-SSA](#)



TE Part # 2151875-1
[OCEAN_2.0_Applicator-S-100F-SSM](#)



TE Part # 63257-1
[CONTACT TERMINAL 22-18 AWG TPBR](#)



TE Part # 61148-1
[BRUSH HOLDER AMPLIVAR 22-17 AWG PHBZ](#)

Customers Also Bought



TE Part #34839
[RING TERMINAL 18-14 AWG BR](#)



TE Part #40955
[RING 20-16 AWG .0295 X .390 TPBR](#)




TE Part #60775-1
[SPADE TERMINAL 18-14 AWG BR](#)




TE Part #61793-1
[RING 18-14 AWG TPST](#)



TE Part #151321-4
[250 FASTON,FLAG,REC.,18-14 AWG, TPBR](#)



TE Part #3-520106-2
[ULTRA-FAST 250 ASY TAB 16-14 AWG TPBR](#)



TE Part #3-520140-2
[ULTRA-FAST 250 ASY REC 16-14 AWG TPBR](#)



TE Part #640052-1
[RING 18-14 AWG SST](#)



TE Part #794273-1
[04P UMNL INTERFACE SEAL](#)



TE Part #794274-1
[04P UMNL WIRE SEAL](#)

Documents



Product Drawings

CONTACT 18-14 AWG NPSTL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62134-2_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62134-2_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62134-2_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.