ENVIRONMENTALLY SEALED TOGGLE

The T9 Toggle Switch is an ideal switch for demanding applications. Qualified to MIL-DTL-3950, this high performance switch is a logical choice for use in environments where sealing and resistance to shock and vibration are required. The T9 is particularly suitable for applications in military, off-highway, aviation, commercial and industrial equipment. This compact, environmentally sealed switch is available in single and double pole configurations with a lever lockout option. Circuitry configurations include two or three positions with many combinations of OFF-ON in momentary and maintained action including ON-ON-ON.


Features:


- Qualified to MIL-DTL-3950
- Commercial version is sealed per IP68S
- Lever lockout option available
- UL, CSA & CE approvals (pending)
- Maintained & momentary toggle action
- Optional panel seal
- RoHS/WEEE/Reach compliant
- Black matte finish available. Contact factory.



Standard Characteristics/Ratings:										
ELECTRICAL RATINGS:	See Product Family Table									
Electrical Life:	20,000 cycles									
Mechanical Life:	40,000 cycles									
Seal:	IP68S									
Operating Temp Range:	-65°C to +71°C									
MATERIALS:										
Toggle:	Stainless steel, passivated									
Bushing & Cover:	Aluminum, clear anodized or zinc alloy									
Case:	Thermoset plastic									
Terminal Hardware:	Included									
Mounting Hardware:	Hex nuts, lockwasher, keyway washer, 0.138-32 UNC-2A screw with lockwasher									

T9 PART NUMBER CODE






Optional Panel Seal P/N 710196, MIL. P/N M5423/16-01

Lever Lockout Configuration Codes


Figures A thru P are schematics to illustrate lockout configurations and momentary positions. They do not represent details of construction.

- A Locked in all three positions
- **B** Locked in Center and Keyway Side position
- **D** Locked out of Center position
- E Locked in Center position
- F Locked in Opposite Keyway position
- G Locked in Keyway Side position
- **H** Locked out of Center and Keyway Side Position
- ${\bf J}$ Locked out of Center and Opposite Keyway position
- \boldsymbol{K} Locked in Center and Opposite Keyway position
- L Locked out of Keyway Side position
- M Locked out of and into Opposite Keyway position
- N Locked out of Opposite Keyway position
- P Locked out of and into Keyway Side position



PRODUCT FAMILY TABLE


COMMERCIAL & MIL TOGGLE SWITCHES





Low level 1	0mA @ 30m	/ (commercia	I version only)


0770 0407	MILL LTADY		CIRCUIT BY	TOGGLE LEVE	R POSITION	ELECTRICAL RATINGS - SEA LEVEL & 65,000 FT							
OTTO PART NO.	MILITARY NO.	DASH NO.	KEYWAY	CENTER	OPP. KEYWAY		28 VDC		II5 VAC				
			I - 2	CENTER	2 - 3	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIV		
		21	ON	OFF	ON						10		
T9-MSI-		22	OFF	NONE	ON	5	20	15	3	15			
		23	ON	NONE	ON	3							
	MS24523-	24	NONE	OFF	ON								
		25	NONE	MOM OFF	ON	4	15	10	2	15	7		
		26	MOM ON	NONE	ON								
		27	MOM ON	OFF	MOM ON								
		28	MOM ON	OF F	NONE								
		29	MOM OFF	NONE	ON								
		30	MOM ON	NONE	OFF								
		31	MOM ON	OF F	ON								
ОТТО	MILITARY	DASH	KEAMAA	CENTER	OPP. KEYWAY		28 VDC			II5 VAC			
PART NO.	NO.	NO.	KEYWAY	1 - 2	2 - 3	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIV		
TO MCI	MCCAECO	32	NONE	ON	MOM ON	4	15	10	2	15	7		
T9-MSI-	MS24523-	33	NONE	ON	ON	5	20	15	3	15	10		

Lever/Lock Single Pole LOCKING CONFIGURATIONS LOCKED OUT OF CENTER POSITION OPPOSITE KEYWAY POSITION LOCKED IN THREE POSITIONS & KEYWAY SIDE POSITION












OTTO 21649

				CIRCUIT B	ELE	CTRICAL R	ATINGS -	EA LEVEL & 65,000 FT					
OTTO BASE	MILITARY	DASH	LOCKOUTS					28 VDC		II5 VAC			
PART NO.	NO.	NO.	(SEE CHART)	KEYWAY I-2	CENTER	OPP. KEYWAY	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE	
				1-2		2-3							
		21	ALL	ON	OFF	ON	_	20		3	٠.,	10	
		22	DFG	OFF	NONE	ON	5		15		15		
		23	DFG	ON	NONE	ON							
T9-MSI-		24	EFKM	NONE	OFF	ON							
		25	F	NONE	OFF (M)	ON	4		15 10	2	15		
	MS24658-	26	F	MOM ON	NONE	ON						7	
		27	ELN	MOM ON	OFF	MOM ON		1.6					
		28	E	MOM ON	OFF	NONE		'					
		29	F	MOM OFF	NONE	ON							
		30	F	MOM ON	NONE	OFF							
		31	EFKLMN	MOM ON	OFF	ON							
0110	MILITARY	DASH	AVAILABLE	V.F. V.W.A.V	CENTER	OPP. KEYWAY		28 VDC			II5 VAC		
BASE NO.	NO.	NO.	LOCKOUT	KEYWAY	1 - 2	2-3	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE	
T9-MS1-	MS24658-	32	E	NONE	ON	MOM ON	4	15	10	2	15	7	
19-M21-	M324638-	33	EFKM	NONE	ON	ON	5	20	15	3	15	10	

COMMERCIAL & MIL TOGGLE SWITCHES

PRODUCT FAMILY TABLE

Double Pole




Low level 10mA @ 30mV (commercial version only)

OTTO BASE	MILITARY	DASH	CIRC	CUIT CONFIGURA	TION	ELECTRICA	L CURRENT	RATINGS (AMPS) - SE	A LEVEL &	65,000 FT		
PART NO.	STANDARD	NO.	KEYWAY	CENTER	OPP. KEYWAY		28 VDC		115 V	AC, 60Hz &	400Hz		
	017070		1-2 / 4-5	CENTER	2-3 / 5-6	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE		
T9-MS2-01	- - - MS27407-	I	ON	2-3 ON 4-5	ON	7	20	15	4	15	15		
T9-MS2-02		2	MOM ON	2-3 ON 4-5	ON	5	18	10	2				
T9-MS2-03		.3	MOM ON	2-3 ON 4-5	MOM ON	,	10	10	2	''	8		
T9-MS2-04	M321401-	4	ON	1-2 ON 5-6	ON	7	20	15	4	15	15		
T9-MS2-05]	5	MOM ON	I-2 ON 5-6	ON	5	18	10	2	11	8		
T9-MS2-06		6	MOM ON	1-2 ON 5-6	MOM ON								
		21	ON	OFF	ON	7	20	15	4	15			
		22	OFF	NONE	ON						10		
		23	ON	NONE	ON								
		24	NONE	OFF	ON								
		25	NONE	MOM OFF	ON			10	2	11	8		
T9-MS2-	MS24524-	26	MOM ON	NONE	ON								
		27	MOM ON	OFF	MOM ON								
		28	MOM ON	OFF	NONE	5	18						
		29	MOM OFF	NONE	ON								
		30	MOM ON	NONE	OFF								
		31	MOM ON	OFF	ON								
OTTO BASE	MILITARY	DASH	KEYWAY	CENTER	OPP. KEYWAY		28 VDC		II5 VAC				
PART NO.	STANDARD	NO.	NC I WAT	1-2 / 4-5	2-3 / 5-6	LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE		
T9-MS2-	MS24524-	32	NONE	ON	MOM ON	5	18	10	2	11	8		
13-M32"	M324324"	33	NONE	ON	ON	7	20	15	4	15	15		



PRODUCT FAMILY TABLE

COMMERCIAL & MIL TOGGLE SWITCHES



0770 0105			AVAILABLE	CIRCUIT CONFIGURATION			SWITCH		ELECT	LECTRICAL RATINGS – SEA LEVEL & 65,000 FT					
OTTO BASE PART NO.	MILITARY STANDARD	DASH NO.	LOCKOUTS	KEYWAY	CENTER	OPP. KEYWAY	POSITION MARKING			28 VDC		115 VA	400Hz		
	OTTHIBITIE		(SEE CHART)	1-2 / 4-5	CENTER	2-3 / 5-6			LAMP	RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE	
		21	ALL	ON	OFF	ON	ON OFF	ON					15	15	
		22	D,F,G	OFF	NONE	ON	OFF	ON	7	20	15	4			
		23	D,F,G	ON	NONE	ON	ON	ON			13				
		24	E,F,K,M	NONE	OFF	ON	OFF	ON							
		25	F	NONE	MOM OFF	ON	OFF	ON	- 						
T9-MS2-	MS24659-	26	F	MOM ON	NONE	ON	ON	ON		18		2	11	8	
		27	E,L,N	MOM ON	OFF	MOM ON	ON OFF	ON							
		28	E	MOM ON	OFF	NONE	ON OFF		5		10				
		29	F	MOM OFF	NONE	ON	OFF	ON							
		30	F	MOM ON	NONE	OFF	ON (OF F							
		31	E,F,K,L,M,N	MOM ON	OFF	ON	ON OFF	ON							
OTTO BASE		DASH	AVAILABLE	KEYWAY	CENTER	OPP. KEYWAY		SWITCH POSITION MARKING LAP		28 VDC			II5 VAC		
PART NO.	STANDARD	NO.	LOCKOUT	REIWAI	1-2 / 4-5	2-3 / 5-6				RESISTIVE	INDUCTIVE	LAMP	RESISTIVE	INDUCTIVE	
T9-MS2-	MS24659-	32	E	NONE	ON	MOM ON	ON	ON	5	18	10	2	Ш	8	
13 M32	M274033-	33	E,F,K,M	NONE	ON	ON	ON	ON	7	20	15	4	15	15	